

NOTES:

MATERIALS

- FERRULE: COPPER ALLOY PER ASTM B139-95
- INSULATION SLEEVE: HEAT-SHRINKABLE, TRANSPARENT BLUE, RADIATION CROSS-LINKED MODIFIED POLYVINYLDENE FLUORIDE.
- SOLDER PERFORM WITH FLUX:
SOLDER: TYPE Sn63 PER ANSI-J-STD-006.
FLUX: TYPE ROM1 PER ANSI-J-STD-004.
- SHIELD: SOLDER IMPREGNATED, FLUX COATED, TIN PLATED COPPER BRAID.
SOLDER: TYPE Sn63 PER ANSI-J-STD-006.
FLUX: TYPE ROM1 PER ANSI-J-STD-004.
- FINISH:
A) FERRULE CADMIUM PLATED IN ACCORDANCE WITH QQ-P-416. OVER A SUITABLE UNDERPLATE.
- INSTALLATION: SEE RAYCHEM INSTALLATION PROCEDURE RPIP-652-35.
- PACKAGING: ONE SPIGOT AND ONE SOLDER SHIELD PER BAG.
10 BAGS IN A BOX.

8 THE VALUES TABLE GIVES GEOMETRICAL GUIDE LINES.
HOWEVER PLATING, SHAPE, DIAMETER OF CABLES CAN BE VARY
AND AN INSTALLATION MUST BE DONE TO GUARANTEE PROPER RESULT.


Ø D OUTSIDE DIA OF JACKETS.		Ø E OUTSIDE DIA OF BRAIDS.		Ø F MAX. OUTSIDE DIA OF WIRES.
MIN.	MAX.	MIN.	MAX.	
.140	.315	.071	.236	.201
[3.55]	[8.0]	[1.8]	[6.0]	[5.1]

MAXIMUM QTY. OF BRAIDS: 4


8

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
D	DRAWING HAS BEEN CONVERTED FROM FRENCH PER T-30412	12/10/2001	M.HIGGY



APPLICATIONS



SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS. DECIMALS .XXX ± .XX ± ANGLES .X ± WEIGHT:	DRAWN	ZS.ORBAN	11/30/2001	tyco /Electronics/Raychem WIRE AND HARNESSING PRODUCTS 307 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025	
	CHECKED				
	APPROVED	M.HIGGY	11/30/2001	TITLE SPIGOT LARGE SIZE WITH SOLDER SHIELD FOR MULTIPORT BACKHELL	
	RPN:				
	CAD NAME	T30412.DWG			
	THIRD ANGLE PROJECTION				
	SIZE	C	CODE IDENT. NO.	06090	DWG. NO.
				ECA-0030	REV D
	DO NOT SCALE THIS DRAWING				SHEET 1 OF 1