



PRODUCT SPECIFICATION

Threadlock

Liquid Properties

Chemical Base	Methacrylate ester
Appearance	Blue liquid
Flashpoint	90°C
Density	1,13
Viscosity (Brookfield) @ 25°C	2000 - 5000 cP Thixotropic

Disclaimer

The data contained within this Technical Data Sheet are furnished for information only and are believed to be reliable at the time of issue. We cannot assume responsibility for results obtained by others over whose methods we have no control. It is the responsibility of the customer to determine the products suitability for use. Adesco and its associated companies accept no liability arising out of the use of this information or the products described herein.

Polymer Properties

Appearance	Blue resin
Temperature range	-55 - 150°C
Cure Speed (handling strength)	15 minutes
Full Cure Time	24 hours

Cured Performance

Break loose strength	22N.m
Prevailing Strength	10N.m

Product Storage

Adesco anaerobics should ideally be stored in original sealed containers until used. Containers should be stored between 10°C and 22°C, avoid exposure to strong light and heat sources. Refrigeration can prolong shelf life.

Adesco

3 Edmund Road, Sheffield, S2 4EB
Tel: 0114 2755884 Fax: 0114 2757169