






AUX. VIEW
SCALE 1:1



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. "XX" REFERS TO QUANTITY OF CIRCUITS
7. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
8. ALL COMPONENTS ARE ROHS COMPLIANT.
9. -59 OPTION: SCREWS SUPPLIED UNASSEMBLED.

5	XX	SCREW, #6-32X.250 PAN HD PH-SL W/SQ WSHR (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW, #6-32 X .250 PAN HD PH-SL (-49 OPTION)	BRASS	NICKEL
3	XX	SCREW, #6-32 X .250 BHD PH-SL (STANDARD)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, STYLE 9, FAST TAB	BRASS	TIN
1	1	BARRIER TERMINAL STRIP	THERMOPLASTIC	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

ADDED -59 OPTION
EC NO: ETC2006-0503
DRW: NEHLE 2006/07/17
CHKD: JMACNEIL 2006/07/19
APPR: RDOSS 2006/07/20

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .03	± .003
1 PLACE	± .06	± .006
ANGULAR	± 2 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
C. YORK

DATE
2003/12/29

CHECKED BY

DATE

APPROVED BY

DATE

MATERIAL NO.
SEE CHART

SCALE
2:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

11.11MM [.437] SR BTS
FT ASSY

MOLEX INCORPORATED

DOCUMENT NO.
SD-38731-001

SHEET NO.
1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

