

REV. Status

REVISION -
01/19/01 RJ

CE DC 9V 300mA POWER SUPPLY

A. Electrical specifications

1. Input voltage: AC 230V $\pm 10\%$ 50Hz ± 0.3 Hz
2. Output voltage and current: DC 9V at 300mA

V_{in}	100% Load	10% Full Load
207	7.18VDC MIN	-
230	8.55-9.45VDC	13.84VDC MAX
253	-	15.33VDC MAX

NOTE: Specification applies after 10 minutes warm-up with 300mA load and at any operating temperature

3. Operating temperature: 0°C to +40°C
4. Storage temperature: -20°C to +85°C
5. Operating and Storage Humidity: 0 to 95% without condensation
6. Withstand voltage: AC 4000Vrms 1 minute @ input to output

- B. Typical performance data test condition: $T_a = +25^\circ\text{C}$, measured after 10 minute warm-up with input at 230V 50Hz



- C. Safety agencies
IEC 65.950, 742
CE Marking

- D. Nameplate:
See drawing P-N1-12429 for details



E. Mechanical Specifications

All dimensions nominal unless otherwise specified



PREPARED BY:

D. Rund

ENGINEER:

R. Jones

QUALITY CONTROL:

D. Kelley

APPROVED:

D. Kelley

DWG CONTROL NO.
P-A7-12571
ACAD\PS\A7125711.DWG

REV
-

CE DC 9V 300mA
POWER SUPPLY

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

416FG41017

MODEL SPECIFICATION

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.