


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs(g) 100 pcs
	MIN. in (mm)	MAX. in (mm)									
SG350LH	.19 (4.8)	4.13 (105)	.064 (1.6)	.330 (8.4)	.393 (10)	.290 (7.4)	.546 (13.9)	15.3 (388.6)	120 (534)	LIGHT HEAVY	1.18 (536)
SG450H	.19 (4.8)	5.20 (132)	.068 (1.7)	.380 (9.7)	.425 (11)	.320 (8.1)	.597 (15.2)	18.6 (471.0)	175 (778)	HEAVY	1.70 (772)

NOTE:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										SUPER-GRIP CABLE TIES	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .020(.5) (.XX) ±.02(.5) ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	3/03/06	FAB		ADDED SG450H	27441	1				DRAWN BY JABO DATE 4/28/05 CHK'D BOBK MAT'L: NYLON 6.6	SCALE NONE
R	4/28/05	JABO	BOBK	DRAWING RELEASED	27441	R	TGS				DRAWING NO. SS-27441
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP			DWG A SIZE
										SHEET 3 OF 3	