

			REVISIONS																																																																															
			REV	DESCRIPTION	DATE	APPROVED																																																																												
			01	RELEASED	7/9/96	<i>DCamelio</i>																																																																												
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A, Fig. 310.1</td><td>Temperature Rating -65°C to +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>Recommended Mating</td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 335</td><td>Torque 7-10 In-Lbs</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR 1.05 + .005f(GHz)</td><td>Mating Characteristics:</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp shall be 115°C</td></tr><tr><td>Insertion Loss (dB MAX) .03√f(GHz)</td><td>Insertion (MAX Lbs) N/A</td><td>Moisture Resistance MIL-STD-202, Method 106, Except Vibration Shall Be Omitted</td></tr><tr><td>RF Leakage (dB MIN) -[60-F(GHz)]</td><td>Withdrawal (MIN Oz) N/A</td><td>Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td>Force to Engage and Disengage (In/Lbs MAX) 2.0</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000</td><td>Center Contact Captivation</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td>Axial (Lbs) 6.0</td><td></td></tr><tr><td>Center Contact 2.0</td><td>Radial (In/Oz) 4.0</td><td></td></tr><tr><td>Outer Contact 2.0</td><td>Cable Retention</td><td></td></tr><tr><td>Cable to Housing N/A</td><td>Axial Force (Lbs) N/A</td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td>Torque (In/Oz) N/A</td><td></td></tr><tr><td>I.R.(Megohms MIN) 10000</td><td>Weight (Grams) TBD</td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.1	Temperature Rating -65°C to +125°C	Frequency Range (GHz) DC to 18	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level 335	Torque 7-10 In-Lbs	Shock MIL-STD-202, Method 213, Condition I	VSWR 1.05 + .005f(GHz)	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp shall be 115°C	Insertion Loss (dB MAX) .03√f(GHz)	Insertion (MAX Lbs) N/A	Moisture Resistance MIL-STD-202, Method 106, Except Vibration Shall Be Omitted	RF Leakage (dB MIN) -[60-F(GHz)]	Withdrawal (MIN Oz) N/A	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	Corona, 70,000 Ft (VRMS MIN) 250	Force to Engage and Disengage (In/Lbs MAX) 2.0		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Center Contact Captivation		Contact Resistance (Milliohms MAX)	Axial (Lbs) 6.0		Center Contact 2.0	Radial (In/Oz) 4.0		Outer Contact 2.0	Cable Retention		Cable to Housing N/A	Axial Force (Lbs) N/A		RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	Torque (In/Oz) N/A		I.R.(Megohms MIN) 10000	Weight (Grams) TBD		<table><tr><td>HOUSING COUPLING NUT</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290</td></tr><tr><td>DIELECTRIC</td><td>TFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290</td></tr><tr><td>RETAINING RING</td><td>BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H</td><td>N/A</td></tr><tr><td>GASKET</td><td>SILICONE RUBBER PER ZZ-R-765</td><td>N/A</td></tr><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON</td><td>DRAWN BY <i>DCamelio</i> DATE 7/9/96</td><td rowspan="2"> AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>FRAC. DEC. ANGLES</td><td>CHECKED BY</td></tr><tr><td>± 1/64 ±.005 ± 1°</td><td>APPROD BY <i>DCamelio</i> 7/9/96</td><td></td></tr><tr><td>These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASS'Y PROCEDURE</td><td></td></tr><tr><td></td><td>NO. AP. N/A</td><td></td></tr></table>			HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290	DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290	RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A	GASKET	SILICONE RUBBER PER ZZ-R-765	N/A	COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY <i>DCamelio</i> DATE 7/9/96	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES	CHECKED BY	± 1/64 ±.005 ± 1°	APPROD BY <i>DCamelio</i> 7/9/96		These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE			NO. AP. N/A	
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.1	Temperature Rating -65°C to +125°C																																																																																
Frequency Range (GHz) DC to 18	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition D																																																																																
Volt Rating (VRMS MAX) @ Sea Level 335	Torque 7-10 In-Lbs	Shock MIL-STD-202, Method 213, Condition I																																																																																
VSWR 1.05 + .005f(GHz)	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp shall be 115°C																																																																																
Insertion Loss (dB MAX) .03√f(GHz)	Insertion (MAX Lbs) N/A	Moisture Resistance MIL-STD-202, Method 106, Except Vibration Shall Be Omitted																																																																																
RF Leakage (dB MIN) -[60-F(GHz)]	Withdrawal (MIN Oz) N/A	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray																																																																																
Corona, 70,000 Ft (VRMS MIN) 250	Force to Engage and Disengage (In/Lbs MAX) 2.0																																																																																	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Center Contact Captivation																																																																																	
Contact Resistance (Milliohms MAX)	Axial (Lbs) 6.0																																																																																	
Center Contact 2.0	Radial (In/Oz) 4.0																																																																																	
Outer Contact 2.0	Cable Retention																																																																																	
Cable to Housing N/A	Axial Force (Lbs) N/A																																																																																	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	Torque (In/Oz) N/A																																																																																	
I.R.(Megohms MIN) 10000	Weight (Grams) TBD																																																																																	
HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290																																																																																
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290																																																																																
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A																																																																																
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A																																																																																
COMPONENT	MATERIAL	FINISH																																																																																
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY <i>DCamelio</i> DATE 7/9/96	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																																
FRAC. DEC. ANGLES	CHECKED BY																																																																																	
± 1/64 ±.005 ± 1°	APPROD BY <i>DCamelio</i> 7/9/96																																																																																	
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE																																																																																	
	NO. AP. N/A																																																																																	
<table><tr><td colspan="2">TITLE OSM FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL</td></tr><tr><td>SIZE B</td><td>CODE IDENT NO. 26805</td></tr><tr><td>SCALE 4:1</td><td>1250-0563-00</td></tr><tr><td colspan="2">SHEET 1 OF 1</td></tr></table>			TITLE OSM FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL		SIZE B	CODE IDENT NO. 26805	SCALE 4:1	1250-0563-00	SHEET 1 OF 1																																																																									
TITLE OSM FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL																																																																																		
SIZE B	CODE IDENT NO. 26805																																																																																	
SCALE 4:1	1250-0563-00																																																																																	
SHEET 1 OF 1																																																																																		