





- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR NATURAL OR LIGHT NATURAL.
PIN CONTACTS: PHOSPHOR BRONZE.
GROUND BUSSES: PHOSPHOR BRONZE.
- 2 PIN CONTACTS: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00254–0.00762[.000100–.000300] TIN–LEAD ON SOLDER TAIL,
ALL OVER 0.00127–0.00254[.000050–.000100] NICKEL ON ENTIRE CONTACT.
GROUND BUSSES: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00254–0.00762[.000100–.000300] TIN–LEAD ON SOLDER TAIL,
ALL OVER 0.00127–0.00254[.000050–.000100] NICKEL ON ENTIRE BUS.
- 3 AMP AND DATE CODE MARKED IN AREA INDICATED, ON SAME SIDE AS POSITION NUMBER 2 INDICATOR.
- 4 ONE GROUND BUS WITH 4 TAILS PER EACH 20 PIN CONTACTS.

OBSOLETE	125.73[4.950]	99	128.22[5.048]	130.81[5.150]	132.44[5.214]	200	149012-9
OBSOLETE	113.03[4.450]	89	115.52[4.548]	118.11[4.650]	119.74[4.714]	180	149012-8
OBSOLETE	100.33[3.950]	79	102.82[4.048]	105.41[4.150]	107.04[4.214]	160	149012-7
OBSOLETE	87.63[3.450]	69	90.12[3.548]	92.71[3.650]	94.34[3.714]	140	149012-6
OBSOLETE	74.93[2.950]	59	77.42[3.048]	80.01[3.150]	81.64[3.214]	120	149012-5
OBSOLETE	62.23[2.450]	49	64.72[2.548]	67.31[2.650]	68.94[2.714]	100	149012-4
	49.53[1.950]	39	52.02[2.048]	54.61[2.150]	56.24[2.214]	80	149012-3
	36.83[1.450]	29	39.32[1.548]	41.91[1.650]	43.54[1.714]	60	149012-2
	24.13[.950]	19	26.62[1.048]	29.21[1.150]	30.84[1.214]	40	149012-1
E		D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. GERACE 11-29-94	 TE Connectivity			
			CHK P. MATAR 11-29-94				NAME
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APD A. MONK 11-29-94		PRODUCT SPEC 108-1272	
		0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± 0.13[.005] 4. PLC ± - ANGLES ± -		APPLICATION SPEC 114-11005		PLUG ASSEMBLY, 18.75[.738] STACK, 4.7[.185] TAIL, BOARD TO BOARD, MICROSTRIP	
				WEIGHT 0.000000		SIZE A1	
MATERIAL 		FINISH 		DRAWING NO 00779		C-149012	
CUSTOMER DRAWING				SCALE 10:1		RESTRICTED TO -	
				SHEET 1 OF 1		REV C	