


215789-1 Product Details



215789-1

TE Internal Number: 215789-1



Superseded

[Search for Replacement Parts](#)

Eurocard Type C

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- Connector
- Receptacle
- Type = Type C
- 96 Positions
- Rows Loaded = A, B, C

[View all Features](#)



Live Product Chat

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Recommended PC Board Hole Pattern](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- [Gender](#) = Receptacle
- [Number of Positions](#) = 96
- [PCB Retention Feature](#) = Yes
- [PCB Mount Angle](#) = Vertical
- [PCB Thickness \(Minimum\) \(mm \[in\]\)](#) = 1.60 [0.063]
- [Post Type](#) = Compliant Post
- [Size](#) = Standard
- [Make First / Break Last](#) = No
- [Bus Type](#) = FUTUREBUS, MULTIBUS (II), NUBUS, VMEbus, VXIBus
- [DIN Level](#) = I
- [Mounting Ears](#) = With
- Toolless (Flat Rock) = No

Termination Related Features:

- [Termination Post Length \(mm \[in\]\)](#) = 4.39 [0.173]

Body Related Features:

- [Type](#) = Type C
- [Rows Loaded](#) = A, B, C
- [PCB Retention Method](#) = ACTION PIN (Compliant) Posts
- [Contact Cross Section \(mm \[in\]\)](#) = 0.64 [.025] Sq.

Contact Related Features:

- Contact Base Material = Phosphor Bronze

Housing Related Features:

- Housing Material = Polyester GF
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [Flux-Tight Coating](#) = Without

Conditions for Usage:

- [Terminate To](#) = Printed Circuit Board
- [High Temperature Housing](#) = No

Other:

- Brand = AMP



BOOKMARK



Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

