






LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	DWN
						APVD
				SEE SHEET 1		


- NOTES:
1. MATERIAL:
HOUSING: THERMOPLASTIC (LCP) WITH 30% G/F, UL94V-0
R-CONTACT/PIN#1: COPPER ALLOY
T-CONTACT/PIN#4: COPPER ALLOY
SHUNT/PIN#3: COPPER ALLOY
GND CONTACT/PIN#5: COPPER ALLOY
2. FINISH:
T&R CONTACT/PIN#1 AND
SHUNT/PIN#3 AND
GND CONTACT/PIN#5: 1.27um[50μ"] MIN. AG PLATING ON OVERALL,
1.27um[50μ"] MIN. NICKEL UNDERPLATED OVERALL.
3. RECOMMENDED PCB THICKNESS: 1.6mm
4. REFLOW SOLDER CAPABLE TO 260°C.
PER TYCO SPEC. 109-201, CONDITION B.



RECOMMENDED PCB LAYOUT <BOTTOM VIEW>
PCB TOLERANCE : ±0.05

DIP TYPE

4A	5-	-4
3A	5-	-3
2A	5-	-2
1A	5-	-1
SCHEMATIC	PART NUMBER	


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LEE	14APR2007	tyco Tyco Holdings (Bermuda)				
		CHK S. HOU	14APR2007	Electronics VII Ltd. Taiwan Branch				
DIMENSIONS: MM		APVD W.J. KE	14APR2007	NAME				
		PRODUCT SPEC 108-57516	ø3.5mm AUDIO JACK, 5 TAILS, SMT TYPE					
0 PLC ± 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 4 PLC ± ANGLES ± 3°		QUALIFICATION TEST REPORT 501-57671						
MATERIAL SEE NOTE		FINISH SEE NOTE	WEIGHT 2.0 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C-1775268	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE —	SHEET 2 OF 4	REV A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.					




SMT TYPE


Notic:



- NOTES:
- MATERIAL:
 - REEL: PS
 - CARRIER: PS
 - COVER TAPE: PE
 - DIMENSION:
 - REEL SIZE: DIA=380mm, W=36.0mm
 - INNER BOX: L=381mm, W=395mm, H=86mm
 - CARTON: L=420mm, W=400mm, H=460mm
 - QUANTITY:
 - 750PCS/REEL
 - 2 REELS/INNER BOX: 1,500PCS
 - 5 INNER BOXS/CARTON: 7,500PCS
 - WEIGHT:


NET WEIGHT: 11KG/CARTON
GROSS WEIGHT: 12KG/CARTON



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LEE 14APR2007		tyco Electronics Tyco Holdings (Bermuda) VII Ltd. Taiwan Branch			
		CHK S. HOU 14APR2007					
		APVD W.J. KE 14APR2007		NAME			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		ø3.5mm AUDIO JACK, 5 TAILS, SMT TYPE			
							
						PRODUCT SPEC	
						—	
						APPLICATION SPEC	
		—					
MATERIAL		FINISH		RESTRICTED TO			
—		—		—			
CUSTOMER DRAWING				SIZE	CAGE CODE		
				A3	00779		
				DRAWING NO	—		
				C=1775268	—		
				SCALE	—		
				SHEET	3 of 4		
				REV	A		

LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1.		

DIP TYPE



- NOTES:
- 1. MATERIAL:
 - 1.1 BAG: PE
 - 1.2 SHIPPING CARTON: CORRUGATED FIBERBOARD
 - 2. DIMENSION:
 - 2.1 SHIPPING CARTON: L=395mm, W=250mm, H=340mm
 - 3. QUANTITY:
 - 3.1 PRIMARY PACKING: 500 PCS/BAG
 - 3.2 SECONDARY PACKING: TYPE A: 7 BAGS/INNER BOX (3,500PCS)
TYPE B: 6 BAGS/INNER BOX (3,000PCS)
 - 3.2 THIRD PACKING: 3 INNER BOXS(=2A+1B)/CARTON (10,000PCS)
 - 4. CARTON WEIGHT:
 - 4.1 NET WEIGHT: 7Kg
 - 4.2 GROSS WEIGHT: 8Kg

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LEE	14APR2007	tyco Electronics Tyco Holdings (Bermuda) VII Ltd. Taiwan Branch		
		CHK S. HOU	14APR2007			
		APVD W.J. KE	14APR2007	NAME ø3.5mm AUDIO JACK, 5 TAILS, SMT TYPE		
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:				
		0 PLC	± -			
		1 PLC	± -			
		2 PLC	± -			
		3 PLC	± -			
		4 PLC	± -			
		ANGLES	± -			
MATERIAL		FINISH				
				SIZE A3	CAGE CODE 00779	DRAWING NO C=1775268
				RESTRICTED TO —		
				SCALE —	SHEET 4 OF 4	REV A