

High Ohmic Value (up to 1.5 G Ω), High Power Resistors (up to 10 W at 25 °C) Thick Film



FEATURES

- High ohmic values up to 1.5 G Ω
- Power rating up to 10 W at +25 °C
- Molded or coated
- Ceramic core
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

DIMENSIONS in millimeters

The diagram illustrates the physical dimensions and specifications for two types of resistors: COATED and MOLDED. Both styles share common lead dimensions: a length of 25 mm from the lead end to the resistor body, a lead diameter of $\varnothing E$, and a 45° chamfer with a maximum depth of 0.25 mm. The COATED resistor features a central body with a diameter of $\varnothing B$, a total length of L (maximum), and mounting holes with a diameter of $\varnothing a \pm 0.02$. The MOLDED resistor has a rectangular body with a diameter of $\varnothing B$ and a lead diameter of $\varnothing E$.

SERIES AND STYLE	A	$\varnothing B$	$\varnothing E \pm 0.1$	WEIGHT g	FINISH
HPS58	6.5 ± 0.2	2.4 ± 0.1	0.6	0.24	Molded
HPS63	10 ± 0.2	3.7 ± 0.1		0.29	
HPS68	15 ± 0.2	5.6 ± 0.3	0.8	0.67	Coated
HPS523	23 ± 2.3	5 ± 0.3		1.23	
HPS923	23 ± 2.5	9 ± 0.5		4.60	
HPS932	32 ± 2.5	9 ± 0.5		5.27	
HPS947	47 ± 2.5	9 ± 0.5		7.18	

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	RESISTANCE RANGE Ω	RATED POWER $P_{25\text{ }^{\circ}\text{C}}$ W	LIMITING ELEMENT VOLTAGE V	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C	CRITICAL RESISTANCE (Ω)	CLIMATIC CATEGORY
HPS58	200 to 100M	1	300	0.5, 1, 2, 5, 10	150	90K	-55 °C/ +200 °C/ 56 days
HPS63	200 to 175M	2	700	0.5, 1, 2, 5, 10	150	245K	
HPS68	300 to 400M	3	1500	0.5, 1, 2, 5, 10	150	750K	
HPS523	800 to 650M	4	2000	0.5, 1, 2, 5, 10	150	1M	
HPS923	1K to 1G	6	2500	0.5, 1, 2, 5, 10	150	1.041M	
HPS932	1K to 1G	8	5000	0.5, 1, 2, 5, 10	150	3.125M	
HPS947	2K to 1.5G	10	8000	0.5, 1, 2, 5, 10	150	6.4M	

MARKING

GEKA trade-mark, series, style, nominal resistance (in Ω), tolerance (in %), letter P for TCR ± 150 ppm/°C, manufacturing date. Because of lack of space, small styles are marked with ohmic value (in Ω), tolerance (in %) and letter P.

ORDERING INFORMATION

HPS	68	50 M Ω	10 %	150 ppm/°C	BL20	e1
MODEL	SIZE	OHMIC VALUE	TOLERANCE	TEMPERATURE COEFFICIENT	PACKAGING	LEAD (Pb)-FREE



GLOBAL PART NUMBER INFORMATION														
H	P	S	0	6	8	5	0	0	5	K	P	B	1	5
GLOBAL MODEL	STYLE		OHMIC VALUE			TOLERANCE		TEMPERATURE COEFFICIENT		PACKAGING			SPECIAL	
HPS	HPS: 58 to 947		The first three digits are significant figures and the last digit specifies the number of zeros to follow. R designates decimal point. 1006 = 100 MΩ 5104 = 5.1 MΩ 3303 = 330 kΩ 5005 = 50 MΩ ...			D = 0.5 % F = 1 % G = 2 % J = 5 % K = 10 %		P = 150 ppm K = 100 ppm		B15 = blister (20 pieces) B19 = blister (30 pieces) A18 = ammpack (400 pieces) A20 = ammpack (500 pieces) B17 = blister (25 pieces) R10 = reel (500 pieces) as applicable			As applicable	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.