

	13	12	11	10	9	8	7	6	5	4	3	2	1		
J	PART NO.	CIRCUITS	LENGTH ±.01 [.25]	WIDTH ±.004 [.10]	NOTES: 1. SUBSTRATE AND COVERLAY MATERIAL IS .001 [25uM] POLYIMIDE. 2. CONDUCTOR IS 1/2 OZ (.0007) [18uM] COPPER. 3. PLATING IS 2 MICRO INCHES MINIMUM OF HARD GOLD OVER 100 MICRO INCHES MINIMUM OF NICKEL. 4. TAIL ENDS ARE .008 [.20] THICK. 5. JUMPER CABLES ARE SUITABLE FOR USE WITH MOLEX 502598 SERIES CONNECTOR.										J
	150150223	23	2.00 [50.8]	.283 [7.2]											J
	150150423	23	4.00 [101.6]	.283 [7.2]											J
	150150623	23	6.00 [152.4]	.283 [7.2]											J
I	150150823	23	8.00 [203.2]	.283 [7.2]	JUMPER END DETAIL 33 CIRCUIT SHOWN	I									
	150151023	23	10.00 [254.0]	.283 [7.2]		I									
	150150225	25	2.00 [50.8]	.307 [7.8]		I									
	150150425	25	4.00 [101.6]	.307 [7.8]		I									
H	150150625	25	6.00 [152.4]	.307 [7.8]	FRONT	H									
	150150825	25	8.00 [203.2]	.307 [7.8]		H									
	150151025	25	10.00 [254.0]	.307 [7.8]		H									
	150150227	27	2.00 [50.8]	.331 [8.4]		H									
G	150150427	27	4.00 [101.6]	.331 [8.4]	REAR	G									
	150150627	27	6.00 [152.4]	.331 [8.4]		G									
	150150827	27	8.00 [203.2]	.331 [8.4]		G									
	150151027	27	10.00 [254.0]	.331 [8.4]		G									
F	150150229	29	2.00 [50.8]	.354 [9.0]	REAR	F									
	150150429	29	4.00 [101.6]	.354 [9.0]		F									
	150150629	29	6.00 [152.4]	.354 [9.0]		F									
	150150829	29	8.00 [203.2]	.354 [9.0]		F									
E	150151029	29	10.00 [254.0]	.354 [9.0]	REAR	E									
	150150233	33	2.00 [50.8]	.403 [10.2]		E									
	150150433	33	4.00 [101.6]	.403 [10.2]		E									
	150150633	33	6.00 [152.4]	.403 [10.2]		E									
D	150150833	33	8.00 [203.2]	.403 [10.2]	REAR	D									
	150151033	33	10.00 [254.0]	.403 [10.2]		D									
	150150239	39	2.00 [50.8]	.472 [12.0]		D									
	150150439	39	4.00 [101.6]	.472 [12.0]		D									
C	150150639	39	6.00 [152.4]	.472 [12.0]	REAR	C									
	150150839	39	8.00 [203.2]	.472 [12.0]		C									
	150151039	39	10.00 [254.0]	.472 [12.0]		C									
	150150245	45	2.00 [50.8]	.543 [13.8]		C									
B	150150445	45	4.00 [101.6]	.543 [13.8]	REAR	B									
	150150645	45	6.00 [152.4]	.543 [13.8]		B									
	150150845	45	8.00 [203.2]	.543 [13.8]		B									
	150151045	45	10.00 [254.0]	.543 [13.8]		B									
A	150150251	51	2.00 [50.8]	.614 [15.6]	REAR	A									
	150150451	51	4.00 [101.6]	.614 [15.6]		A									
	150150651	51	6.00 [152.4]	.614 [15.6]		A									
	150150851	51	8.00 [203.2]	.614 [15.6]		A									
	150151051	51	10.00 [254.0]	.614 [15.6]											

15015

NUMBER OF CIRCUITS

LENGTH

SERIES NUMBER

PART NUMBER CONSTRUCTION

JUMPER END DETAIL

33 CIRCUIT SHOWN

FRONT

REAR

QUALITY SYMBOL

GENERAL TOLERANCES (UNLESS SPECIFIED)

DIMENSION STYLE

SCALE

DESIGN UNITS

THIRD ANGLE PROJECTION

TITLE

APPROVED BY

DATE

MATERIAL NO.

DOCUMENT NO.

SHEET NO.

SIZE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION