








LOC	DIST	REVISIONS				
		REV	DATE	BY	CHKD	APPD
AD	00	A	REV PER EC 0512-0302-05	06DEC05	BC	GS
		B	ECR-10-018652	10SEP10	JS	MQW
		C	ECO-11-024491	13DEC11	SY	MQW

- 1 MATERIAL:
CONTACT: PHOSPHER BRONZE.
HOUSING: GLASS FILLED POLYESTER.
- 2 GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION
PIN: 0.5µm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4 PLATED THROUGH HOLES AT 2 x 1.5mm GRID. 128 TOTAL HOLES.
- 5 CONNECTOR PRINTED WITH PART NUMBER AND DATE CODE THIS SIDE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.



SECTION W-W



RECOMMENDED PCB HOLE LAYOUT
COMPONENT SIDE
SCALE 2.5:1

PCB HOLE DIM ACTION PIN
DRILLED HOLE: 0.7±0.025
FIN HOLE: 0.55 TO 0.65mm
Cu-thks: 0.025 TO 0.050mm
SnPb-thks: 0.004 TO 0.010mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	14DEC05	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK G. SKIPPER	14DEC05	NAME		RECEPTACLE ASSEMBLY, Z-PACK 2mm HM, TYPE D	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. SKIPPER	14DEC05	PRODUCT SPEC		SIZE CAGE CODE DRAWING NO	
0-PLG ±0.2		APPLICATION SPEC		WEIGHT		RESTRICTED TO	
1-PLG ±0.10		NAME		SCALE		SHEET	
2-PLG ±0.10		PART NUMBER		5:1		1 OF 1	
3-PLG ±0.10		CUSTOMER DRAWING		A1 00779		REV C	
4-PLG ±0.10		SCALE		5:1		SHEET	
ANGLES		SCALE		5:1		SHEET	
SEE TABLE		SCALE		5:1		SHEET	