

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		B1	REVISED PER ECO-11-005027	11MAR11	RK HMR

D

C

B

A


D

C

B

A

SIDE VIEW
(SEE NOTE 3)



SPECIFICATIONS:

LAMP DISSIPATION: 1.2W MAX.
INSULATION RESISTANCE: 100 MEGOHMS MIN.
DIELECTRIC STRENGTH: 2000 VAC.
OPERATING TEMPERATURE: -20°C TO +50°C
(-4°F TO +122°F).

NOTES:

- LAMP IS T 3/4 MIDGET FLANGE BASE TYPE (LAMP NOT SUPPLIED).
- 164 IS NON-DILTIGHT SERIES, 165 IS DILTIGHT SERIES.
- VIEWS INCLUDE PLASTIC SHROUDS FOR AVAILABLE LENS SETS, (NOT SUPPLIED).

- 4 THE PLATINGS CONTAINED IN THIS PART SHALL CONTAIN NO LEAD.
- 5 PRELIMINARY PART, NOT RELEASED FOR PRODUCTION.

1571542-4	165TZ	4 5
1571542-3	164TZ	
1571542-2	164SZ	
1571542-1	164EZ	
5-1437569-9	165TZ	
5-1437569-3	165SZ	
4-1437569-6	165EZ	
4-1437569-1	164TZ	
3-1437569-2	164SZ	
1437569-8	164EZ	
PART No.	MODEL NUMBER	COMMENTS

REF AUGAT 81091

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S KIRCORIAN 5-18-94	TE TE Connectivity			
DIMENSIONS: INCHES		CHK W THIA 5-19-94				
		APVD W THIA 5-19-94	NAME PILOT LIGHT 164/165 Z			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=2-1437569-4	RESTRICTED TO -
		FINISH -	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
					REV B1	