




1

.000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL ENTIRE CONTACT

2

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

3

.000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

4

POINT OF MEASUREMENT FOR PLATING THICKNESS

5

GOLD PLATING NOT REQUIRED IN THIS AREA

6

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

7

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.

8

.000100-.000200 BRIGHT TIN OVER .000030 NICKEL ENTIRE CONTACT.

9

.000100-.000200 MATTE TIN OVER .000030 NICKEL ENTIRE CONTACT.

10

.000015 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

11

.000030 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D KEITZER
12-14-88

CHK
S. SHUEY
12-15-88

APVD
C.SINISI
12-16-88

PRODUCT SPEC

APPLICATION SPEC

WEIGHT
-

CUSTOMER DRAWING

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$ -

1 PLC $\pm$ -

2 PLC $\pm$ -

3 PLC $\pm$.005

4 PLC $\pm$ -

ANGLES $\pm$ -

FINISH

SEE TABLE

MATERIAL
PHOS BRONZE

TE Connectivity

PIN, AMPMODU, MTE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-104506

RESTRICTED TO
-

SCALE
10:1

SHEET
1 of 1

REV
H1