




1-1563878-1 AS SHOWN
1-1563878-1 wie gezeigt

NOTES
Bemerkungen

1 TE LOGO
TE Logo

2 ASSY PN, PRODUCTION DATE (CALENDAR DAY/YEAR):
MARKING OPTIONAL AS LASER ENGRAVING OR
LASER WITH COLOR CHANGE
Assy PN, Produktionsdatum (Kalendertag/Jahr):
Beschriftung wahlweise als Lasengravur oder Laser mit Farbumschlag



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Shilpa Bhavani CHN Elitrop		 TE Connectivity	
DIMENSIONS: MASSING (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ACC. TO ISO 2768 ACC. TO ISO 2768-1		NAME 15POS. AMP MCP 2.8/1.5K. REC HSG. ASSY 15pos. AMP MCP 2.8/1.5K. Buchsengehaeuse HDSCS- GROUP E	
		APXID C. Barwin PRODUCT SPEC 108-94020 APPLICATION SPEC VERABE (TRANS) SPEC 118-10756 WEIGHT SEW HWT 32.4g		SIZE A 1 CASE CODE 000779 DRAWING NO 01563878 SCALE Blatt 2:1 SHEET 1 OF 1 REV J2	
MATERIAL SEE TABLE siehe Tabelle		ANGLE 90° ± 0.2° 118-10756 REC HSG. ASSY SEE TABLE siehe Tabelle		RESTRICTED TO OUR PUR	

