





SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG

REVISIONS				DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
			ASH	16-08-10	JAG	17-08-10	XXX	30-08-10	



Part Number Table

Description	Part Number
Transformer, Power, Rectifier	SPC20992

Electrical Characteristics:

Primary:

117V +/- 15%
FREQUENCY = (50.60) Hz

Secondary:

25.2vct at 2.0ARMS

Regulation:


13.13% RMS (approx)

Transformer Isolation:

Pri/Sec 1500v
Wind/Care 1500v

LEADS:

- Primary: 22 AWG
- Secondary: 18 AWG
- UL 1015 105°C PVC
- Length: 6.0 ±0.5
- Ends Stripped: 0.5 ±0.125



DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED, ALL
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

ASH

DATE:

16-08-10

DRAWING TITLE:

Transformer, Power, Rectifier

CHECKED BY:

JAG

DATE:

19-08-10

SIZE

DWG. NO.

XXX

DATE:

30-08-10

SCALE:

NTS

U.O.M.: INCHES [mm]

XXX

SHEET:

1

OF

1

ELECTRONIC FILE

92N4400

REV

XXX