




CE52**S**00



CE52**S**K0

Materials :

- * Insulator : Glass filled polyester UL 94V-0
- * Contact : Phosphor Bronze
- * Shield : Brass with 80μ" Nickel over 50μ" Cu
- * Solder tail plating : Tin plated over Nickel

Ordering Code

CE52 06 S A 1 00
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Contacts: 03~08 Circuits
- ③ Connector type: S=Receptacle
- ④ Plating code:
A=Selective Gold flash plated over 1.27μm(50μ") Nickel
B=Selective 0.38μm(15μ") Gold plated over 1.27μm(50μ") Nickel
C=Selective 0.76μm(30μ") Gold plated over 1.27μm(50μ") Nickel
- ⑤ Color code: 1=Black, 6=Green, 8=Purple
- ⑥ Other option: 00=With grounding hook
K0=With grounding pegs

Circuits	3	4	5	6	7	8
Arrangement of Contact						
P.C Board Layout						
Tolerance .X ±0.10/.004 .XX ±0.05/.002						

Lead Free Process

RoHS Compliant

④					DATE	UNIT: mm / inch	TITLE: FULLY SHELED MINI DIN		
③							SOCKET WITH HOOK & GROUNDING		
②							MATERIAL:		
①	Enya	9/18-12'	ECN12231-0/ECR12064-0				FINISH:		
SYM	NAME	DATE	REVISIONS						

CIVILUX CORP
2012.10.11
ISSUED

DRAWN BY: Enya
ENGINEER: Eisley
CHECKED BY: Eisley
APPROVED BY: David

9/18-12'
9/18-12'
9/18-12'
9/18-12'

UNIT: mm / inch
TOLERANCE
UNLESS OTHERWISE SPECIFIED
.X ± 0.30/.012
.XX ± 0.20/.008
.XXX ±



瀚荃股份有限公司
CviLux Corporation

DRAWING NO. CE5201SB PART NO. CE52**S***0
SCALE 3 / 1 SHEET 1 OF 1