



FEATURES:

- Mounts in panels from 1.60 (.063) to 9.53 (.375) thick.
- Accepts wires or plugs up to 2.16 (.085) DIA. with insulation up to 4.06 (.160) DIA.

MATERIALS:

Body: Bright Tin Plated Brass

Insulation: Polycarbonate

Lockwasher: Steel

Hex Nut: Brass

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 630 VAC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 4770-*

*=Color, -0 Black, -2 Red,

Ordering Example: 4770-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4770-5](#) [4770-4](#) [4770-9](#) [4770-6](#)