




- 1

1.27μm [.000050] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 2


0.76μm [.000030] MIN GOLD IN LOCALIZED
PLATE AREA, 0.25μm [.000010] MIN
GOLD ON THE REMAINDER ALL OVER
1.27μm [.000050] MIN NICKEL.
- 3

2.54μm [.000100] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.
- 5

1.27μm [.000050] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.

4	SMALL PACK	2	202236-8	
	STANDARD	2	202236-7	
	SMALL PACK	5	202236-6	
	STANDARD	5	202236-5	
3	SMALL PACK	1	202236-4	
	SMALL PACK	2	202236-3	
	STANDARD	1	202236-2	
	STANDARD	2	202236-1	
FINISH SOLDER TAB		PACKAGING TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL27SEP90		TE Connectivity									
DIMENSIONS: mm [INCHES]		CHK J.McCLINTON15DEC90											
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD A. BOULLIANNE15DEC90		NAME PIN ASSEMBLY, LOOSE PIECE, TYPE III+ -								
			PRODUCT SPEC										
			APPLICATION SPEC										
			-										
MATERIAL SEE CALL OUT		FINISH PIN BODY:SEE TABLE		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C-202236		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 8:1		SHEET 1 of 1		REV T1			