




LOC	DIST	REVISIONS				
G	86	P	LTR	DESCRIPTION	DATE	APVD
			F	REV PER 0G3A-0637-01	030CT02	JR MS

- 1 TIN PLATE 0.00381 [0.000150] MIN THK PER ASTM B 545
- 2 CLEANED, UNPLATED
- 3 PREPRODUCTION - FASR REQ



2-	31-324452-0
1-	324452
FINISH	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM	01JUL96	AMP AMP Incorporated Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH	02JUL96						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY	02JUL96	NAME WIRE SPLICE, PARALLEL, AMPOWER™ WIRE SIZE: 600 MCM				
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC —						
			APPLICATION SPEC —		SIZE A3	CAGE CODE 00779	DRAWING NO C-324452		
	MATERIAL COPPER PER ASTM B-75 ANNEALED		FINISH SEE TABLE		WEIGHT .146 lbs		SCALE 2:1	SHEET 1 OF 1	REV F
					CUSTOMER DRAWING				