

multicomp

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.




SPC-PD08.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECK'D	DATE	APPR'D	DATE
1820	A	RELEASED	HO	3/24/05	JN	04/25/08	JN	04/25/08

TO-92

DIM.	MIN.	MAX.
A	4.32	5.33
B	4.45	5.20
C	3.18	4.19
D	0.41	0.55
E	0.35	0.50
F	S*	
G	1.14	1.40
H	1.14	1.53
K	12.70	—



Description: The 78L24 is a positive 3-terminal voltage regulator in a TO-92 type package suitable for numerous applications requiring up to 100mA. This device features thermal shutdown and current limiting making the 78L24 remarkably rugged. In most applications, no external components are required for operation. The 78L24 is useful for on-card regulation or any other application where a regulated negative voltage at a modest current level is needed. This device offers a substantial advantage over the common resistor/Zener diode approach.

Features:

- No External Components Required
- Internal Short-Circuit Current Limiting
- Internal Thermal Overload Protection

Absolute Maximum Ratings:

- Input Voltage, $V_{in} = 40V$
- Internal Power Dissipation (Note 1), $P_D =$ Internally Limited
- Operating Junction Temperature Range, $T_{Jop} = 0^\circ C$ to $+70^\circ C$
- Maximum Junction Temperature, $T_J = +125^\circ C$
- Storage Temperature Range, $T_{stg} = -55^\circ C$ to $+150^\circ C$
- Lead Temperature (During Soldering, 10sec.), $T_L = +300^\circ C$

Electrical Characteristics: ($V_{OT} = 0 + 125^\circ C$, $V_{out} = 24V$, $V_{in} = 33V$, $I_D = 40mA$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$, Note 2, unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Output Voltage	V_O	$T_J = +25^\circ C$	23.0	24.0	25.0	V
		1mA $\circ$ $I_D \circ$ 100mA, 27V $\circ$ $V_{in} \circ$ 38V	22.8	24.0	25.2	V
Line Regulation	Reg_{line}	$T_J = +25^\circ C$, 27V $\circ$ $V_{in} \circ$ 38V	—	—	350	mV
Load Regulation	Reg_{load}	$T_J = +25^\circ C$, 1mA $\circ$ $I_D \circ$ 100mA	—	—	200	mV
Quiescent Current	I_Q	$T_J = +125^\circ C$	—	—	6	mA
Quiescent Current Change	I_Q	With line, 28V $\circ$ $V_{in} \circ$ 38V	—	—	1.5	mA
Output Noise Voltage	V_n	$T_J = +25^\circ C$, $f = 10Hz$ to 10kHz	—	200	—	μV
Ripple Rejection	RR	29V $\circ$ $V_{in} \circ$ 35V, $f = 120Hz$	31	47	—	dB
Drop Out Voltage	V_{DO}	$T_J = +25^\circ C$, $I_D = 40mA$	—	1.7	—	V

Notes:

- 1— Thermal resistance, junction-to-ambient is $+180^\circ C/W$ when mounted with 0.40 inch leads on a P.C. board, and $+160^\circ C/W$ when mounted with 0.25 inch leads on a P.C. board.
- 2— To ensure constant junction temperature, low duty cycle pulse testing is used.

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:			
HISHAM ODISH	3/24/05	Voltage Regulator, Bipolar, Plastic, TO-92, Positive			
CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
Jason Nash	04/25/08	A	79L24	35C0957.DWG	A
APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: MILLIMETERS	SHEET: 1 OF 1
Jason Nash	04/25/08				