




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-11-025318	19DEC11	KH	GJ
	B2	REVISED PER ECR-17-002254	16FEB17	ST	TD



- 1 CONTINUOUS STRIP ON REEL.
-  2 VERTICAL BURRS NOT TO EXCEED 0.13 [.005] ALONG THIS EDGE.
- 3 BACK OUT TORQUE OF SCREW TO BE A MIN OF 5 INCH LBS AND A MAX OF 25 INCH LBS.
- 4 REFERENCE APPLICATOR LOG SHEET FOR CRIMP INFORMATION.
- 5 PART TO HAVE HARDENED NUTS



2.79-4.06 [.110-.160] DIA	#16-#12 AWG	521843-1
INSULATION RANGE	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 13SEP05		 TE Connectivity	
		CHK DONALD DECKER 13SEP05			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38[.015] 3 PLC ± - 4 PLC ± - ANGLES ± ± -		NAME	
		DONALD DECKER APVD 13SEP05 PRODUCT SPEC 108-1191 APPLICATION SPEC 114-2087		TERMINAL, SUB-ASSEMBLY, POWER RING	
MATERIAL SEE COMPONENT		FINISH SEE COMPONENT		SIZE A2	CAGE CODE 00779
		WEIGHT 0.000000		DRAWING NO C-521843	
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1
				REV R2	