



**Material and Finish**

Insulator: HTN thermoplastic,
UL94V-0 rated, black or white color,
Reflow Process Compatible-
Recommended Soldering Temperature:
230°C for 30 seconds, 260°C max.

Front Shield, Grounding Strip: brass,
0.30mm thick, 120u" nickel plated over
50u" copper underplate

Rear Shield: cold rolled steel, 0.30mm thick,
120u" nickel plated over 50u" copper
underplate

Contact Material: phosphor bronze

Contact Plating Options:

Standard: gold flash on contact area,
120u" min. tin/lead on soldertails,
all over 50u" min. nickel underplate

-30 Option: 30u" gold on contact area,
120u" min. tin/lead on soldertails,
all over 50u" min. nickel underplate

Recommended PCB Thickness: 1.6mm

Specifications:

Contact Current Rating: 1A max.

Contact Resistance: 30 milliohms max.

Insulation Resistance: 1000 Megohms min.

Dielectric Withstanding Voltage: 750V AC

Insertion Force: 3.57kg max.

Extraction Force: 1.02kg min.

Operating Temperature: -25°C to +80°C


Durability: 1500 mating cycles min.

Part Number	Contact Area Plating	Insulator Color
KUSBL-AS-2-N-W	Gold Flash (standard)	White
KUSBL-AS-2-N-W-30	30u" Gold (-30 option)	
KUSBL-AS-2-N-B	Gold Flash (standard)	Black
KUSBL-AS-2-N-B-30	30u" Gold (-30 option)	



Tolerances
X.X ± 0.35
X.XX ± 0.25
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	1/22/03	New Drawing	T. Gokcek	C. Leiva	T. Gokcek	1/15/03
A1	3/14/03	Release Drawing	T. Gokcek	H.MA		
A2	6/25/04	ECO#04-029	H. MA	C. Leiva		



UNITS
mm

KUSBL-AS-2-N-x-yy

x - insulator color
yy - plating option

Stacked A-Type USB Socket

Low Profile Mount, PCB Mount, Right Angle



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KUSBL-AS-2-N-B](#) [KUSBL-AS-2-N-B-30](#) [KUSBL-AS-2-N-W](#) [KUSBL-AS-2-N-W-30](#)