




SECT. G-G



SECT. H-H



黄銅 BRASS (t=0.203)	部分金メッキ : 0.76 μm MIN. SELECTIVE GOLD : 0.76 μm MIN. 部分半田メッキ : 2 μm MIN. SELECTIVE TIN-LEAD : 2 μm MIN. ニッケルメッキ (下地) : 1.27 μm MIN. NICKEL : 1.27 μm MIN.	0.6	2.3	2.3	0.4	1.65	1.8	Ø 0.9-1.8	#22-28	39-00-0088	5558 GS2L	バラ状 LOOSE		
		0.9	4.5	3.6	0.5	2.3	1.9	Ø 1.3-3.1	#18-24	↑ ↓	-0087 -0054	↑ ↓	GS2 GSL	バラ状 LOOSE
										39-00-0053	5558 GS	連鎖状 CHAIN		
MATERIAL	メッキ・FINISH	F	E	D	C	B	A	被覆外形 INS. RANGE	適用電線 WIRE RANGE	EDP NO.	ENG. NO.	端子形状 FORM		

注記
NOTES.

- 適合ハウジング : 5557 シリーズ
APPLICABLE HOUSING : 5557 SERIES.
- 嵌合相手 : 5558, 5566, 5569 シリーズ
MATES WITH TERMINAL : 5558 , 5566 , 5569 SERIES.
- 適用電線が #22-28 の製品のセレーション数は 1 とする。
THE NUMBER OF SERRATIONS TO BE ONE
FOR WIRE RANGE #22-28.

REVISED
EC NO: J2005-1103
DRAWN:MEDIA
CHKD:KTOYODA
APPR:NUKITA
2004/10/20
2004/10/20
2004/10/22

GENERAL TOLERANCES
(UNLESS SPECIFIED)

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE
MM ONLY

DRAWN BY H. HIRAMO	DATE 1991/04/08
CHECKED BY M. FUKUSI	DATE 1991/04/08
APPROVED BY M. ENOMOT	DATE 1991/04/08
MATERIAL NO.	
SEE CHART	

SCALE
10:1

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

NEW MINI. FIT CONN.
CRIMP PIN



MOLEX INCORPORATED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DOCUMENT NO.
SD-5558GS**

SHEET NO.
1 OF 1