

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	M.3	REVISED PER ECR-17-018200	09JAN2018	BDA	SG



- 1 MATERIAL: CONNECTOR - NYLON UL94-V2 (WHITE)
CONTACTS - 0.30[.012] THICK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 641438-2 THRU 2-641438-4).
(MATTE TIN PLATE 0.00203[.000080] MIN. THICK
FOR CONTACTS 3-641438-2 THRU 5-641438-4).
- 2 CONTACTS ACCEPT #24 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX
INSULATION DIA.
- 3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.
- 4 HOUSING FEATURES: CLOSED END. .
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.

6


OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7

OBsolete PARTS



SECTION A-A

TIN		91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	5-641438-4
		55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	4-641438-5
		43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	4-641438-2
		31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	3-641438-9
		19.81 [1.780]	23.88 [1.940]	27.74 [1.092]	6	3-641438-6
		11.89 [1.468]	15.95 [1.628]	19.81 [1.780]	4	3-641438-4
		7.92 [1.312]	11.99 [1.472]	15.85 [1.624]	3	3-641438-3
		3.96 [1.156]	8.03 [1.316]	11.89 [1.468]	2	3-641438-2
△ SUPERSEDED		91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	2-641438-4
△ SUPERSEDED		55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	1-641438-5
△ SUPERSEDED		43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	1-641438-2
△ SUPERSEDED	TIN-LEAD	31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	641438-9
△ SUPERSEDED		19.81 [1.780]	23.88 [1.940]	27.74 [1.092]	6	641438-6
△ SUPERSEDED		11.89 [1.468]	15.95 [1.628]	19.81 [1.780]	4	641438-4
△ SUPERSEDED		7.92 [1.312]	11.99 [1.472]	15.85 [1.624]	3	641438-3
△ SUPERSEDED		3.96 [1.156]	8.03 [1.316]	11.89 [1.468]	2	641438-2
FINISH		C	B	A	NO. OF CIRCUITS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		TE Connectivity		
		0 PLC ± -		NAME		
		1 PLC ± -				
		2 PLC ± 0.13[.005]				
		3 PLC ± -				
4 PLC ± -		4 RLC ± -		MTA 156 POSTED CONNECTOR ASSEMBLY 24 AWG		
ANGLES		± -				
FINISH		-				
MATERIAL		-				
		WEIGHT		SIZE CAGE CODE DRAWING NO		
				A1 00779 C 641438		
		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 of 1 REV M.3		