





PNEUMATIC

SERVO
LATCH PLATE

CAM POSITIONS



HOLDDOWN SET-UP

FEED TRACK POSITION
GUIDE BY INSULATION BARREL

Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION


DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2003

C


B

A


FEED TYPE MECHANICAL




PNEUMATIC








SERVO LATCH PLATE



CAM POSITIONS



PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)



THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND THE USER SHALL BE CONTACTED FOR THE LATEST REVISION.		OWN Y. YIN	15NOV2011	TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK G. BAILEY	15NOV2011	NAME Ocean Side Feed Applicator	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.02 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±0.0005 FINISH		APVD S. XI	15NOV2011	PRODUCT SPEC APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE A1 00779 C=2151205	
		Customer Accessible Production Drawing		RESTRICTED TO SCALE 1:1 SHEET 4 OF 4 REV B	