





REV	DOCUMENT	CHANGED BY	CHECK
5	0011614	KSR	04MAR05

HONEYWELL  
PART NUMBER  
5EN320-6

6 FAA-PMA



NOTES

- CORROSION RESISTANT STEEL ENCLOSURE
- SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- CIRCUIT DIAGRAM, CATALOG LISTING, DATE CODE, FED. MFG. CODE AND FAA-PMA ARE SHOWN ON NAMEPLATE
- COINCIDENCE OF OPERATING AND RELEASING POINTS: .015 INCH OF PLUNGER TRAVEL
- HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
- FOR MANUFACTURING DETAILS SEE ASSEMBLY DRAWING 5EN320-6 FOR FAA-PMA.

CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE ----- 6-12 LBS		CONTACT ARRANGEMENT	
FULL OVERTRAVEL FORCE ----- 30 LBS MAX		S P D T (4)	
RELEASE FORCE ----- 4 LBS MIN		LOAD	
PRETRAVEL ----- .040 MAX		28 VDC	
DIFFERENTIAL TRAVEL ----- .030 MAX		SEA LEVEL	
OVERTRAVEL ----- .500 MIN		50,000 FT	
RES		4	4
IND		2	2
MOTOR		4	
LAMP			

DESIGN UNITS: INCH  
TOLERANCES UNLESS NOTED:

NO PLACE X ±  
ONE PLACE .X ±  
TWO PLACE .XX ±  
THREE PLACE .XXX ±  
FOUR PLACE .XXXX ±  
ANGLES ±

DRAWN SJB 18JUN79  
CHECK GLH 11JUL79

THIS DRAWING COVERS A PROPRIETARY ITEM  
AND IS THE PROPERTY OF HONEYWELL.  
THIS DRAWING IS NOT TO BE COPIED OR USED  
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994  
OTHER HONEYWELL ENGINEERING  
STANDARDS MAY APPLY

TITLE  
SWITCH - ENCLOSED

SIZE TYPE DRAWING NAME REV  
B I 5EN320-6 5  
SCALE 1:1 WEIGHT 15.3 OZ MAX SHEET 1 OF 1

**Honeywell**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[5EN320-6](#)