




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
HB

DIST

REVISIONS

P

LTR

DESCRIPTION

ECN

DATE

DWN

APVD

⑤

SDT-S-118DMR,601	1461056-9	18V	SDT-S-118DMR	h
SDT-S-148DMR,601	1461056-8	48V	SDT-S-148DMR	g
SDT-S-124DMR,601	1461056-7	24V	SDT-S-124DMR	f
SDT-S-112DMR,601	1461056-6	12V	SDT-S-112DMR	e
SDT-S-109DMR,601	1461056-5	9V	SDT-S-109DMR	d
SDT-S-106DMR,601	1461056-4	6V	SDT-S-106DMR	c
SDT-S-105DMR,601	1461056-3	5V	SDT-S-105DMR	b
SDT-S-103DMR,601	1461056-2	3V	SDT-S-103DMR	a
TE TYPE NAME	PART NO	PART B	PART A	No.

RELAY TYPE

		EPOXY RESIN	SEAL (BASE & TERMINAL)	15
		EPOXY RESIN	SEAL (BASE & YOKE)	14
		3UEW	MAGNETIC WIRE	13
94V-0		P.B.T	CASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		NYRON	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shenzhen,China

NAME

SDT-DMR SPEC,601

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

①

1461056-2

CUSTOMER DRAWING

SCALE

SHEET 2 OF 2

REV c