


**NEW!**

SMT Power Transformer

For Linear Technology LT1725
Isolated Flyback Controller



- Can be used in isolated and nonisolated designs
- Operates with 36 – 72 Volts input; can be used for PoE.
- 1500 Vrms isolation between the primary and the secondary

Core material Ferrite

Terminations RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 5.1 g

Ambient temperature –40°C to +125°C

Storage temperature Component: –40°C to +125°C.
Packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)
38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 200 per 13" reel Plastic tape: 44 mm wide, 0.35 mm thick, 28 mm pocket spacing, 9.6 mm pocket depth

PCB washing Only pure water or alcohol recommended

Part number ¹	Power	L at 0 A ² ±10% (μH)	L at I _{pk} ³ min (μH)	DCR max (Ohms)			Leakage L max ⁵ (μH)	Turns ratio		I _{pk} ³ (A)	Output ⁷
				pri	sec ⁴	bias		pri : sec ⁶	pri : bias		
C1048-AL_	13 W	94.0	84.6	0.210	0.01	0.453	3.9	1 : 0.12	1 : 0.47	1.2	5 V, 2 A

1. When ordering, please specify **packaging** code:

C1048-AL D

Packaging: **D** = 13" machine ready reel. EIA-481 embossed plastic tape (200 per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter D instead.

2. Inductance is for the primary, measured at 250 kHz, 0.3 Vrms, 0 Adc.

3. Peak primary current drawn at minimum input voltage.

4. DCR is for both windings of the secondary connected in parallel.

5. Leakage inductance is for the primary winding with the secondary windings shorted.




6. Turns ratio is with the secondary windings connected in parallel.

7. Output is with the secondary windings connected in parallel. Output of the bias winding with a 15 V, 0.2 A.

8. Operating temperature range –40°C to +125°C.

9. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Secondary windings to be connected in parallel on PC board

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 452 Revised 10/28/08

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web http://www.coilcraft.com