

SLOAN AG

Birmannsgasse 8
CH-4009 Basel
Tel. ++41 61 264 10 60
Fax. ++41 61 261 10 75
info@sloan-basel.com




BA9S



White based 5mm LED's

Easy replacement of filament bulbs
other colours and voltages on request

Part No:	Emitted Colour	Electro-optical-characteristics of used LED Ta=25C°, If=20mA					Forward Voltage VF[V]	Lens Colour	Storage Temp. [C°]	Operating Temp. [C°]
		Chromaticity Coordinates	Luminous Intensity [mcd]			Viewing Angle 2Θ1/2				
			min.	typ.	max.					
BA9S-L5W50NBSA xx	white	x = 0.32 y = 0.31	580	690	805	70°	5.0	milky	-40~+100	-30~+80
BA9S-L5W52NBSA xx			2060	2500	3000	50°		water clear		
BA9S-L5W54NBSA xx			7800	9200	11000	20°				
BA9S-L5W50NBSB xx	white	x = 0.32 y = 0.31	580	690	805	70°	12.0	milky	-40~+100	-30~+80
BA9S-L5W52NBSB xx			2060	2500	3000	50°		water clear		
BA9S-L5W54NBSB xx			7800	9200	11000	20°				
BA9S-L5W50NBSD xx	white	x = 0.32 y = 0.31	580	690	805	70°	24.0	milky	-40~+100	-30~+80
BA9S-L5W52NBSD xx			2060	2500	3000	50°		water clear		
BA9S-L5W54NBSD xx			7800	9200	11000	20°				








xx = 01

02

03

04

05



1. All dimensions are in millimeters.
2. Tolerance is ± 0.2 mm unless otherwise specified.
3. Specifications are subject to change without notice