


A B C D E F G H

Maximum Electric Rating: 600V
 Maximum Electric Current
 22-16AWG/0.5-1.5mm²: 19A
 16-14AWG/1.5-2.5mm²: 27A
 12-10AWG/4-6mm²: 48A
 Shrinking Temperature: ≥150°C
 Operating Temperature: -40°C ~120°C
 Shrinking Ratio: 3:1
 Terminal Body: Copper
 Insulation: PE
 Plating: Tin



Wire Range mm ² /Awg	Item No.	Stud Size		Dimension (mm/inch)				Insulation Color
		Stud	d2	W	L	D	d1	
0.5~1.5mm ² 22-16AWG	311043SSEL	#8	4.2	6.6	27	4.3	1.7	Red
	311053SSEL	#10	5.2	8	29			
	311064SSEL	1/4	6.3	11.6	35			
	311084SEL	5/16	8.4	11.6	33.8			
	311010SEL	3/8	10.5	13.6	39			
1.5~2.5mm ² 16-14AWG	315043SSEL	#8	4.2	6.6	27	5	2.3	Blue
	315053SSEL	#10	5.2	8.6	29.3			
	315064SEL	1/4	6.3	12	36.7			
	315084SEL	5/16	8.3	12	34.8			
	315010SEL	3/8	10.5	13.6	39.2			
4~6mm ² 10-12AWG	313043SSEL	#8	4.2	7.2	34.6	6.7	3.5	Yellow
	313053SEL	#10	5.2	9.6	39.2			
	313064SSEL	1/4	6.3	12	43.2			
	313084SEL	5/16	8.2	15	44.6			
	313010SEL	3/8	10.4	15	44			

Heat Shrinkable Ring connector Series