




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	MATERIAL	"A" +/- .062	"B" +/- .062	INSIDE NOMINAL DIAMETER	MARKER ACROSS	TUBING COLOR	PKG. QTY.	SEE STYLE
H100X025H1T-2	B	GMUHS	1.00 [25.4]	3.50 [88.9]	1/8 in. [3.1 mm]	2	WHITE	1000	A
H200X025H1T-2	A		2.00 [50.8]			1	WHITE	500	
H100X025H2T-2	B		1.00 [25.4]			2	YELLOW	1000	
H200X025H2T-2	A		2.00 [50.8]			1	YELLOW	500	
H100X025H1T-2-B	B		1.00 [25.4]			2	WHITE	5000	B
H200X025H1T-2-B	A		2.00 [50.8]			1	WHITE	2500	
H100X025H2T-2-B	B		1.00 [25.4]			2	YELLOW	5000	
H200X025H2T-2-B	A		2.00 [50.8]			1	YELLOW	2500	

NOTES:
1. MILLIMETER ARE IN [].



							TITLE H***X025H*T-2 TWO-SIDED HEAT SHRINK LABEL CUSTOMER DRAWING						
							ITEM REVISION NAME I00472PE/03						
							DATASET FILE NAME I00472PE_DC_C10636/03C						
2	1/22/14	RVU	SEWH	MSAD	UPDATE THE CURRENT PANDUIT LOGO.	GAECN01391	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .12 [3.04] .xxx ± .020 [.508] .xx ± .062 [1.57] ANGLES ±  THIRD ANGLE PROJECTION					MATERIAL: HEAT SHRINK TUBING, GMUHS31 DRAWING NUMBER: C10636	
1	5/21/09	RVU		SCWE	ADD NEW PARTS: H100X025H1T-2-B, H200X025H1T-2-B, H100X025H2T-2-B, H200X025H2T-2-B. ADD NEW VIEW OF STYLE B. "B" +/- .062 WAS +/- .050, ETC.	5700							
0	9/09/08	RVU		SCWE	DRAWING RELEASE.	5540							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE		
							RVU	9/09/08	SCWE	NTS	SHT 1 OF 1 A		