




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		H1	REVISED PER ECO-11-005027	11MAR11	RK	HMR

NOTE: THIS DRAWING IS A CONTINUATION OF
THE 87022 SERIES POSTS



- 1

.000030 GOLD OVER .000050 NICKEL.
- 2

APPLICATOR CUT-OFF DIMENSION.
- 3

.000015 GOLD OVER .000050 NICKEL.
- 5

.000050 GOLD OVER .000050 NICKEL.
- 8

.000010 GOLD OVER .000050 NICKEL
- 9

ADVANCE PRODUCTION NO. ASSIGNED.
- 10

.000100 MIN BRIGHT TIN LEAD OVER .000050 NICKEL.
- 11

POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 12

OBSOLETE PART NO.
- 13

.000030 MIN GOLD IN CONTACT AREA "F" .000100-.000200 MATTE TIN-LEAD IN SOLDER AREA "G" ALL OVER .000050 NICKEL.

	.187	.180	.090	.090	.437	.227	.210	13	3-87878-3
	-	-	-	.250	.660	.165	.495	5	3-87878-2
12	-	-	.235	.100	.753	.475	.278	5	3-87878-1
12	-	-	-	-	.485	.255	.230	10	3-87878-0
12	-	-	.165	.230	.790	.330	.460	3	2-87878-8
12	-	-	.165	.100	.608	.330	.278	3	2-87878-6
12	-	-	-	.100	.621	.381	.240	3	2-87878-4
12	-	-	.480	.100	1.190	.960	.230	1	2-87878-2
12	-	-	.580	.100	1.390	1.160	.230	1	2-87878-0
12	-	-	.200	.100	.680	.450	.230	1	1-87878-8
12	-	-	-	-	1.115	.255	.860	10	1-87878-7
12	-	-	.600	.100	1.478	1.200	.278	5	1-87878-6
12	-	-	.385	.100	1.053	.775	.278	3	1-87878-4
12	-	-	-	.250	.695	.200	.495	1	1-87878-2
12	-	-	-	.165	.495	.165	.330	1	1-87878-0
	-	-	.235	.100	.753	.475	.278	1	87878-8
	-	-	-	.100	.437	.227	.210	1	87878-6
12	-	-	-	.430	1.115	.255	.860	3	87878-5
12	-	-	-	-	.508	.230	.287	10	87878-4
12	-	-	-	.100	.508	.230	.287	1	87878-3
12	-	-	.350	.100	.993	.715	.287	1	87878-1
	G	F	E	D	C	B	A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
PHOS BRONZE

SEE TABLE

DWN
L.A.MAYER

CHK
-

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

3-11-77

TE Connectivity

NAME
POST .025 SQUARE, UNINSULATED
MOD II

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=87878

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
H1