



DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION





NOTES:

- 1 PHOSPHORBRONZE # 4 HD / THICKNESS 0,8mm
- 2 2,54µm Sn OVER
1,25µm MIN. NICKEL.
- 3 PLATING: UNDERLAYER; 1,25µm-2,00µm NICKEL
- 4 PLATING: 1.25 - 2.5 NICKEL OVER ALL
- ZONE X ; 3µm Ag MIN.
ZONE Y ; 2,54µm-5,00µm Sn
ZONE X ; 1 - 3µm SN

J2

P.C.B. HOLE DIM. ACTION PIN			
DRILLED HOLE	:1,6	±0,025	mm
FIN. HOLE	:1,39	-0,05	mm
AFTER REFLOW	:1,37	-0,05	mm
Cu-thks	:0,025	to 0,075	mm
Sn-thks or			
SnPb-thks	:0,004	to 0,010	mm



-	-	-	-	-
-	-	-	-	-
J2	ECR-07-018177	Hassel	Bleicher	10-APR-07
J1	Sn-thks or added	MAH.	ZITZ	21-MAY-03
J	DIM. max. 11 ADD. Pb REM.	MAH.	ZITZ	24-APR-03
H1	DIMENSION ADDED	MAH.		26-NOV-02
H	EH00-1341-01	RvH		30-11-01
E	EH00-0806-01	RvH		19-07-01
REV.	ECN No.	DRW.	APVD	DATE
LTR.				

REVISION RECORD

CUSTOMER DRAWING		FINISH		MATERIAL		PARTNUMBER		Rev		
		tyco <i>Electronics</i>		TYCO ELECTRONICS NEDERLAND B.V. 's-HERTOGENBOSCH, THE NETHERLANDS						
		THIS DRAWING IS UNPUBLISHED				RELEASED FOR PUBLICATION - , 19-				
		© COPYRIGHT 19- BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.								
		DR. J.v.LIEMPT.		DATE 02.01.90		WIRE RANGE -		NAME .250 SRS TAB WITH ACTION-PIN FOR POSTITIVE LOCK RECEPTACLE (FOR 1,6-3,2 PC.B. THICKNESS)		REV.DATE D M Y
CHK. A. BIJNEN		DATE 30-11-01`		INSUL.RANGE -		301101				
APP. A. BIJNEN		DATE 30-11-01`		SIZE A3	SHEET 1 OF 1	DWG. No. C-216842			REV.LTR. J2	

.250 SRS TAB WITH ACTION-PIN
FOR POSITIVE LOCK RECEPTACLE
(FOR 1,6-3,2 PC.B. THICKNESS)

8

7

6

5

4

3

2

1