


Ceramic Disc Capacitors (Safety Regulations)

Type TS IEC60384-14 Sub-class Y2/X1

Type NS-A IEC384-14 Sub-class Y1/X1

Type BE 250 VAC For Japan Domestic Safety



■ Features

- Related by IEC60384-14 2nd Ed. and approved by European Safety Regulations (Types TS and NS-A)
- Reinforced Body Insulation /0.4mm min. approved by BSI, VDE (Type NS-A)
- Flame-retardant insulating coating applied
- Easy mounting through kinked Lead and Radial Taping

■ Recommended Applications

- Interference suppressor for AC Primary Line of electronic equipments.

■ Explanation of Part Numbers

E	C	K	N	T	S	1	0	2	M	E		Examples
Product Code		Lead Style		Type Name		Nominal Capacitance		Cap. Tolerance		Temp. Char		Suffix
Code	Class	Code	Style	Code	Type	Ex.	Cap.	Code	Cap. Tol.	Code	Char.	
ECK	Class 2	A	Kinked Lead Bulk	TS	Type TS	101	100 pF	K	±10 %	B	B/Y5P	
		N	Kinked Lead Taped	NA	Type NS-A	102	1000 pF	M	±20 %	E	E/Y5U	
		D*	Straight Lead Bulk	BE	Type BE	222	2200 pF	Z	+80, -20 %	F	F/Y5V	
		Z*	Straight Lead Taped			472	4700 pF					
		R*	Crimped Lead Taped			103	10000 pF					

*:These code are not standard style

■ Specifications

Characteristics	Type TS	Type NS-A	Type BE
Related Standards	IEC 60384-14(Y2 and X1) BSI, VDE, SEV, SEMKO FIMKO, NEMKO, DEMKO UL, CSA	IEC 60384-14(Y1 and X1) BSI, VDE, SEV, SEMKO FIMKO, NEMKO, DEMKO UL, CSA	Japan Domestic Safety
Operating Temperature Range	-25 to 125 °C		-25 to 85 °C
Rated Voltage	250 VAC/440 VAC		250 VAC
Dielectric Withstanding Voltage	2600 VAC for 1 minute	4000 VAC for 1 minute	1500 VAC for 1 minute
Capacitance	Within the tolerance, when measured at 1 kHz ± 20 %, 1 Vrms, and 20 °C		
Dissipation Factor (tanδ)	tan δ ≤ 0.025, when measured at 1 kHz ± 20 %, 1 Vrms, and 20 °C		tan δ ≤ 0.025 for Char.E tan δ ≤ 0.05 for Char.F at 1 kHz ±20 %, 1 Vrms, and 20 °C
Insulation Resistance	10000 MΩ min at 500 VDC 1 minute electrification.		
Temperature Characteristics	Char.	max. Cap. Change	Temperature Range
	B	±10 %	-25 to 85 °C
	E	+20, -55 %	-25 to 85 °C
	F	+30, -80 %	-25 to 85 °C

■ Precautions for Handling

See Page 57 to 58


■ Packaging Information

See Page 59 to 60

■ Dimensions in mm (not to scale)

Standard lead style are kinked Lead and Kinked Lead Taping as below.
As usual style as Straight Lead, Straight Lead Taping and Crimped Lead Taping are available on special order.


● Kinked Lead Type




Note:Tolerance of Lead Space

Dim. F(Nominal)	Tolerance of Dim. F
5.0	±1.0
7.5	±1.5
10.0	±1.5 $\begin{smallmatrix} +1.5 \\ -1.0 \end{smallmatrix}$ for Type NS-A

● Straight Lead Type (For reference)




● Kinked Lead Taping




Taping Type Symbol	N0	N1	N2
P	12.7±1.0	15.0±2.0	30.0±2.0
P ₀	12.7±0.3	15.0±0.3	15.0±0.3
F	5.0±0.8	7.5±1.0	7.5±1.0
P ₁	3.85±0.70	3.75±0.80	3.75±0.80
P ₂	6.35±1.30	7.5±1.5	7.5±1.5
D	To comply with each individual specification		
W	18.0 ^{+1.0} _{-0.5}		
W ₀	10.0 min.		
W ₁	9.0±0.5		
W ₂	3.0 max.		
H ₀	18.0 ^{+2.0} ₀		
e	4.0 max.		
ϕD ₀	4.0±0.2		
ϕd	0.60±0.05	0.65±0.05	
t ₁	0.6±0.3		
t ₂	1.5 max.		
T	To comply with each individual specification		
Δh ₁ , Δh ₂	2.0 max.		
L	11.0 max.		

Under kinked lead style are applied to only 3300 pF and over have a lead space (F) 7.5 mm of Type TS



Same dimensions as Type N0, N1 except for special dimensions.



■ Rating and Characteristics

● Type TS (IEC60384-14 Sub-class Y2, X1)

Cap. in pF	Cap. Tol. (%)	Temp. Char.	Dimensions in mm		Kinked Lead Type (Bulk)			Kinked Lead Taped Type			
			D	T max.	Part Number	Dim. in mm		Part Number	Taped Type	Dim. in mm	
						F	d			F	d
100	±10 or ±20	B/Y5P	7.0±1.0	7.0	ECKATS101□B	7.5	0.65	ECKNTS101□B	N1	7.5	0.65
150	±10 or ±20	B/Y5P	7.0±1.0	7.0	ECKATS151□B	7.5	0.65	ECKNTS151□B	N1	7.5	0.65
220	±10 or ±20	B/Y5P	7.0±1.0	7.0	ECKATS221□B	7.5	0.65	ECKNTS221□B	N1	7.5	0.65
330	±10 or ±20	B/Y5P	7.0±1.0	7.0	ECKATS331□B	7.5	0.65	ECKNTS331□B	N1	7.5	0.65
470	±10 or ±20	B/Y5P	7.0±1.0	7.0	ECKATS471□B	7.5	0.65	ECKNTS471□B	N1	7.5	0.65
680	±10 or ±20	B/Y5P	8.0±1.0	7.0	ECKATS681□B	7.5	0.65	ECKNTS681□B	N1	7.5	0.65
1000	±20	E/Y5U	7.0±1.0	7.0	ECKATS102ME	7.5	0.65	ECKNTS102ME	N1	7.5	0.65
1500	±20	E/Y5U	8.0±1.0	7.0	ECKATS152ME	7.5	0.65	ECKNTS152ME	N1	7.5	0.65
2200	±20	E/Y5U	9.0±1.0	7.0	ECKATS222ME	7.5	0.65	ECKNTS222ME	N1	7.5	0.65
3300	±20	E/Y5U	11.5±1.0	7.0	ECKATS332ME	7.5	0.65	ECKNTS332ME	N1	7.5	0.65
4700	±20	E/Y5U	14.0±1.0	7.0	ECKATS472ME	10.0	0.65	ECKNTS472ME	N2	7.5	0.65
4700	±20	F/Y5V	11.5±1.0	7.0	ECKATS472MF	7.5	0.65	ECKNTS472MF	N1	7.5	0.65
10000	±20	F/Y5V	16.0±1.5	7.0	ECKATS103MF	10.0	0.65	ECKNTS103MF	N2	7.5	0.65

Note: □-- Capacitance Tolerance Code K (±10 %) or M(±20 %)

● Type NS-A (IEC60384-14 Sub-class Y1, X1)

Cap. in pF	Cap. Tol. (%)	Temp. Char.	Dimensions in mm		Kinked Lead Type (Bulk)		
			D max.	T max.	Part Number	Dim. in mm	
						F	d
100	±10 or ±20	B/Y5P	11.0	8.0	ECKANA101□B	10.0	0.65
220	±10 or ±20	B/Y5P	11.0	8.0	ECKANA221□B	10.0	0.65
330	±10 or ±20	B/Y5P	11.0	8.0	ECKANA331□B	10.0	0.65
470	±10 or ±20	B/Y5P	11.0	8.0	ECKANA471□B	10.0	0.65
1000	±10 or ±20	B/Y5P	11.0	8.0	ECKANA102□B	10.0	0.65
1000	±20	E/Y5U	10.0	8.0	ECKANA102ME	10.0	0.65
1500	±20	E/Y5U	11.0	8.0	ECKANA152ME	10.0	0.65
2200	±20	E/Y5U	11.0	8.0	ECKANA222ME	10.0	0.65
3300	±20	E/Y5U	13.0	8.0	ECKANA332ME	10.0	0.65
4700	±20	E/Y5U	16.0	8.0	ECKANA472ME	10.0	0.65

Note 1: Reinforced Body Insulation for 0.4 mm min. approved by BSI, VDE Approved

2: Radial Taped versions are available. (Lead Spacing is 10.0 mm only)




3: □-- Capacitance Tolerance Code k (±10 %) or M(±20 %)

● Type BE (250 VAC For Japan Domestic Safety)



Cap. in pF	Cap. Tol. (%)	Temp. Char.	Dimensions in mm		Kinked Lead Type (Bulk)			Kinked Lead Taped Type			
			D max.	T max.	Part Number	Dim. in mm		Part Number	Taped Type	Dim. in mm	
						F	d			F	d
1000	+80 -20	E/Y5U	7.0	5.0	ECKABE102ZE	7.5	0.65	ECKNBE102ZE	N1	7.5	0.65
2200	+80 -20	E/Y5U	8.0	5.0	ECKABE222ZE	7.5	0.65	ECKNBE222ZE	N1	7.5	0.65
3300	+80 -20	E/Y5U	9.0	5.0	ECKABE332ZE	7.5	0.65	ECKNBE332ZE	N1	7.5	0.65
4700	+80 -20	E/Y5U	11.0	5.0	ECKABE472ZE	7.5	0.65	ECKNBE472ZE	N1	7.5	0.65
4700	+80 -20	F/Y5V	8.0	5.0	ECKABE472ZF	7.5	0.65	ECKNBE472ZF	N1	7.5	0.65
10000	+80 -20	F/Y5V	11.0	5.0	ECKABE103ZF	7.5	0.65	ECKNBE103ZF	N1	7.5	0.65

Note: Lead spacing (Dim. F) of 5.0 mm is available instead of 7.5 mm for special order

■ Typical Temperature Characteristics (Type TS, Type NS-A)







■ Impedance vs. Frequency Characteristics



■ Current vs. Voltage (Leakage Current Characteristics)

Conditions Temperature: 20 °C, Applied Voltage: Sine Wave 60 Hz



Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use.
Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.