








HOLE LAYOUT $\varnothing 0.05$



Specifications:

Contact rating: 0.3A, 30V DC
 Contact resistance: 20mOhm max.
 Insulation resistance: 100MOhm min. at 500V DC for 1 minute
 Dielectric strength: 500V AC (50/60Hz, 2mA) for 1 minute
 Operating temperature: -10°C to +60°C
 Mechanical life: 10 000 cycles
 Operating force: 200 +/-100gf
 Soldering conditions: 260 +/-5°C, 5 +/-1sec.
 Material: Terminal: brass strip, silver plated
 Contact clip: phosphor bronze, silver plated
 Steel ball: carbon steel, natural
 Spring: SWC, temper
 Base: phenolic resin, natural
 Frame: steel, nickel plated
 Slider: POM, black

CIRCUIT DIAGRAM
C: COMMON PIN
BOTTOM VIEW



Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	MFP 1220	
			09/10	dr		
					knitter-switch	30 21 75
Modifications	Date	Name				Page 1/1