

8467 8467-0-15-XX-21-XX-04-0 Hex press-fit in .036 plated thru hole	6192 6192-0-15-XX-21-XX-04-0 Square press-fit in .032 plated thru hole	9553 9553-0-15-XX-X1-XX-04-0 Hex press-fit in .041 plated thru hole	5531 5531-0-15-XX-21-XX-10-0 Hex press-fit in .041 plated thru hole
7553 7553-0-15-XX-11-XX-10-0 Hex press-fit in .041 plated thru hole	9407 9407-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	9462 9462-0-15-XX-21-XX-04-0 Hex press-fit in .043 plated thru hole	1147 1147-0-18-XX-21-XX-10-0 Press-fit in .043 min. mounting hole
3061 3061-0-19-XX-21-XX-10-0 Wire Termination	0579 0579-0-15-XX-X1-XX-10-0 Press-fit in .040 mounting hole	8874 8874-0-15-XX-11-XX-10-0 Bottom entry Surface mount	0613 0613-0-15-XX-21-XX-10-0 Press-fit in .047 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 100μ" TIN/LEAD OVER NICKEL
84 100μ" TIN OVER NICKEL
27 30μ" GOLD OVER NICKEL



SELECT CONTACT

#11 or #21 CONTACT (DATA ON PAGE 217)