



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES

CONTACT MOLEX

FIND DISTRIBUTOR

Home: PCB Receptacles >

Part Number: 22-02-1115

2.50mm Pitch KK® PC Board Connector, Top Entry, 11 Circuits



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	7534
Category:	PCB Receptacles
Overview:	KK® Interconnect System - Molex
Engineering/Old PN:	753411C

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to [Part Detail](#) ▾Mates With Part(s):
[3094](#), [3202](#), [3022](#)**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****General**

Status	Obsolete
Category	PCB Receptacles
Series	7534
Application	Board-to-Board, Signal
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753739482

Physical

Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural (White)
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Compliant	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.251/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Temperature Range - Operating	0°C to +75°C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact

2.5A

Voltage - Maximum

250V

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

Material Info

Engineering Number	753411C
--------------------	---------

PRODUCTS

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

QUICK LINKS

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

RESOURCES

Supply Chain Transparency
Business Continuity
Compliance
Ecocare
Feedback / Help
Jobs
Legal / Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

STAY CONNECTED