


Model 1432

Banana Jack to Pin Tip Plug



Model 1432
Banana Jack to Pin Tip Plug



Features

- Permits banana plug cords to be used with equipment having pin tip jacks.

Materials

Banana Jack:

Material: Brass rod per ASTM B16-85, Temper H02.

Finish: Nickel plated per QQ-N-290, Class 2,
200/300 micro-inches.

Pin Tip Plug:

Body: Brass rod per ASTM B16-85, Temper H02.

Finish: Nickel plate per QQ-N-290, Class 2,
200/300 micro-inches.

Insulation:

Material: Polypropylene molded to Banana Plug and Pin Tip bodies.

Marking: "1432, POMONA ELECTRONICS,
CALIF."

Specifications

Operating Voltage:

Hands free usage in controlled voltage environments: 3000 Vrms maximum.

For CE compliance: not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Operating Temperature: +50°C (+122°F) Max.

Current: 5 Amperes

Ordering Information

Model: 1432-*

*=Color, -0 (Black), -2 (Red)

Ordering Example: 1432-2 (Color is Red)

Other colors are available upon request.

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.