


8.5 mm Diameter Fully Sealed Container Cermet Trimmer



FEATURES

- Industrial grade
 - High quality cermet resistive track:
 - 1 W at 70 °C, P8ST
 - 0.5 W at 70 °C, P8SX and P8SY
 - Test according to CECC 41000 or IEC 60393-1
 - Wide resistance range (10 Ω to 2.2 MΩ)
 - Material categorization: For definitions of compliance please see www.vishay.com/doc/299912
- 

RoHS
COMPLIANT




The P8S series trimmers are well adapted for all industrial applications as their maximum resistance contact variation is within 3 % of R_n and as they are fully sealed.


For more stringent requirements the P8P series is recommended.

DIMENSIONS in millimeters (± 0.5 mm)


P8SX



P8SY



P8ST



**Consult Vishay Sfernice for
panel sealed type**

**ELECTRICAL SPECIFICATIONS**

Resistive element		Cermet
Electrical travel		270° ± 15°
Resistance range		10 Ω to 2.2 MΩ
Standard series E3		1 - 2.2 - 4.7 and on request 1 - 2 - 5
Tolerance	standard	± 10 %
	on request	± 5 %
Power rating	P8SX, P8SY	0.5 W at 70 °C
	P8ST	1 W at 70 °C
Power rating chart	The chart shows the power rating in Watts versus ambient temperature in degrees Celsius. The x-axis ranges from 0 to 140 °C, and the y-axis ranges from 0 to 1.5 W. The P8ST series (1 W) has a constant power rating of 1 W up to 70 °C, then decreases linearly to 0 W at 125 °C. The P8SX - P8SY series (0.5 W) has a constant power rating of 0.5 W up to 70 °C, then decreases linearly to 0 W at 125 °C.	
Circuit diagram	The circuit diagram shows a variable resistor with three terminals: a (1), b (2), and c (3). Terminal b (2) is the wiper, and the arrow indicates clockwise (cw) rotation.	
Temperature coefficient		See Standard Resistance Element Table
Limiting element voltage (linear law)		250 V
Contact resistance variation		3 % R _n or 3 Ω
End resistance (typical)		1 Ω
Dielectric strength (RMS)		1000 V
Insulation resistance (500 V _{DC})		1 GΩ

MECHANICAL SPECIFICATIONS

Mechanical travel		300° ± 5°
Operating torque (max. Ncm)		3
End stop torque (max. Ncm)		6
Unit weight (max. g)	P8SX, P8SY P8ST	1.1 3.6
Terminals		SnAg alloy (code e2)

ENVIRONMENTAL SPECIFICATIONS

Temperature range		- 55 °C to + 125 °C
Climatic category		55/125/56
Sealing		IP67 Fully sealed



PERFORMANCES			
TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS	
		$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)
Load life	1000 h at rated power 90'/30' - ambient temperature 70 °C	± 2 % Contact res. variation: < 3 % Rn	± 3 %
Climatic sequence	Phase A dry heat 100 °C Phase B damp heat Phase C cold - 55 °C Phase D damp heat 5 cycles	± 0.5 %	± 1 %
Long term damp heat	56 days 40 °C, 93 % RH	± 1 % Dielectric strength: 1000 V _{RMS} Insulation resistance: > 10 ⁴ MΩ	± 2 %
Rapid temperature change	5 cycles - 55 °C to + 125 °C	± 0.5 %	$\Delta V_{1-2}/\Delta V_{1-3}$ ≤ ± 1 %
Shock	50 g at 11 ms 3 successive shocks in 3 directions	± 0.2 %	± 0.5 %
Vibration	10 Hz to 55 Hz 0.75 mm or 10 g during 6 h	± 0.2 %	$\Delta V_{1-2}/\Delta V_{1-3}$ ≤ ± 0.5 %
Rotational life	200 cycles	± 3 % Contact res. variation: < 3 % Rn	

STANDARD RESISTANCE ELEMENT DATA							
STANDARD RESISTANCE VALUES	P8SX, P8SY			P8ST			TYPICAL TCR - 55 °C to + 125 °C
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH WIPER	
Ω	W	V	mA	W	V	mA	ppm/°C
10	0.5	2.2	224	1	3.16	316	± 100
22	0.5	3.3	150	1	4.69	213	
47	0.5	4.8	103	1	6.86	146	
100	0.5	7.0	70	1	10.0	100	
220	0.5	10.5	47	1	14.8	67	
470	0.5	15.3	32	1	21.7	46	
1K	0.5	22.4	22	1	31.6	32	
2.2K	0.5	33.2	15	1	46.9	21	
4.7K	0.5	48.5	10	1	68.6	15	
10K	0.5	70.7	7.0	1	100	10	
22K	0.5	105	4.8	1	148	6.7	
47K	0.5	153	3.2	1	217	4.6	
100K	0.5	224	2.2	0.63	250	2.5	
220K	0.28	250	1.1	0.28	250	1.1	
470K	0.13	250	0.53	0.13	250	0.53	
1M	0.06	250	0.25	0.06	250	0.25	
2.2M	0.028	250	0.11	0.03	250	0.11	



MARKING

- Vishay trademark
- Model
- Style
- Ohmic value (in Ω , k Ω , M Ω)
- Tolerance (in %)
- Manufacturing date
- Marking of terminal: 3

PACKAGING

- In plastic box of 50 pieces, code B25 (BL50)

ORDERING INFORMATION (part number)

P	8	S	X	1	0	4	K	B	2	5				
MODEL	STYLE			OHMIC VALUE			TOLERANCE	PACKAGING CODE			SPECIAL NUMBER			
P8	ST SX SY			From 10 Ω to 2.2 M Ω 103 = 10K			K = 10 % On request: J = 5 %	B25 = Box 50 pieces			(If applicable) Given by Vishay for custom design			

PART NUMBER DESCRIPTION (for information only)

P8	S	X	100K	10 %		BL	e2
MODEL	STYLE	STYLE	VALUE	TOLERANCE	SPECIAL	PACKAGING	LEAD FINISH



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.