




AD6025GP SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG24


Specifications(Nominal)

*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x25	AD0612HB-A71GP(P)	◎	12	0.11	1.32	4500	0.611 21.597	0.235 5.969	35.3	77.0
	AD0612UB-A71GP(P)	◎	12	0.22	2.64	5500	0.752 26.566	0.347 8.813	41.4	
	AD0612XB-A71GP(P)	◎	12	0.28	3.60	6500	0.899 31.770	0.489 12.420	44.3	
	AD0612VB-A71GP(P)	◎	12	0.38	4.56	7500	1.056 37.310	0.688 17.475	50.0	
	AD0612EB-A71GP(PCU)	◎	12	0.60	7.20	9000	1.256 44.400	0.945 24.003	52.5	
	AD0624HB-A71GP(P)	◎	24	0.08	1.92	4500	0.611 21.597	0.235 5.969	35.3	
	AD0624UB-A71GP(P)	◎	24	0.11	2.64	5500	0.752 26.566	0.347 8.813	41.4	
	AD0624XB-A71GP(P)	◎	24	0.14	3.36	6500	0.899 31.770	0.489 12.420	44.3	
	AD0624VB-A71GP(P)	◎	24	0.20	4.80	7500	1.056 37.310	0.688 17.475	50.0	
	AD0624EB-A71GP(PCU)	◎	24	0.28	6.72	9000	1.256 44.400	0.945 24.003	52.5	
	AD0648HB-A71GP(P)	◎	48	0.04	1.92	4500	0.611 21.597	0.235 5.969	35.3	
	AD0648UB-A71GP(P)	◎	48	0.06	2.88	5500	0.752 26.566	0.347 8.813	41.4	
	AD0648XB-A71GP(P)	◎	48	0.07	3.36	6500	0.899 31.770	0.489 12.420	44.3	
	AD0648VB-A71GP(P)	◎	48	0.09	4.32	7500	1.056 37.310	0.688 17.475	50.0	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓						✓	✓

*Safety approvals

✓	✓		✓	✓