

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

43255-0129

Status:

Active

Overview:

MLX™ Power Connectors

Description:

6.35mm Pitch MLX™ Power Connector Header, 2.13mm Contact Diameter, Vertical, with Plastic Polarizing Peg, 4 Circuits, PA Polyamide Nylon 6/6 94V-2, Tin (Sn) Plating, Natural (Nylon Off Natural), Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PSX-42002-0001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

PCB Headers

43255

Board-to-Board, Power, Wire-to-Board

High Vibration Application

MLX™ Power Connectors

MLX™

800753948914

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

No

4

4

Natural

50

No

94V-2

No

Yes

Yes

30.35mm

Phosphor Bronze

Tin

Tin

Nylon

2.631/g

1

Vertical

4.30mm

Yes

Yes

1.60mm

Tray

6.35mm

6.35mm

Yes

Yes

Fully

No

No

-55°C to +105°C



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

43255Series

Mates With

42021 MLX™ Power Crimp Housing Plug, 42023 MLX Crimp Terminal, 42024 MLX Crimp Terminal

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	12A, 20A
Voltage - Maximum	600V
Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)
Material Info	
Reference - Drawing Numbers	
Product Specification	PSX-42002-0001
Sales Drawing	SDA-43255-00**

This document was generated on 09/02/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

43255-0129