







- ① 0.000762 MIN THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- ② 0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- ③ 0.0015 - 0.0040 THK BRIGHT TIN.
4. WIRE RANGE: 20 - 24 AWG.
5. INSULATION RANGE 0.89 - 1.524.
- ⑥ AMP LOGO LOCATED APPROXIMATELY AS SHOWN.
- ⑦ 0.000762 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.
- ⑧ 0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.
- ⑨ 0.00102 MIN THK GOLD STRIPE IN THE GOLD PLATE AREA,
BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.



SECTION B - B
SCALE 20:1




SECTION A - A
SCALE 20:1



3 DIMENSIONAL VIEW
SCALE 8:1

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 12-OCT-1999 CHK K. COBLE 12-OCT-1999 APVD K. COBLE 12-OCT-1999		 TE Connectivity		NUMBER	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±0.3° FINISH		NAME CONTACT, RECEPTACLE, CRIMP, SNAP-IN, MICRO MATE-N-LOK(TM)		DATE	
MATERIAL 0.2 PH BRZ		PRODUCT SPEC 108-1836 APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C-794606		RESTRICTED TO -	
SEE TABLE		CUSTOMER DRAWING		SCALE 10:1		SHEET OF REV H3	