


AP-ITA 7529 - S/12

SCHEMA FORATURA CIRCUITO, SPESSORE 1.6 ± 0.2
(PCB HOLE PATTERN THICKNESS 1.6 ± 0.2)



- | | | | | | | | |
|--|--|--|--|--|--|--|--|
| | | | | CUSTOMER DWG.
FOR REFERENCE ONLY | | DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO | |
| | | | | THIS DRAWING IS UNPUBLISHED | | RELEASE FOR PUBLICATION | |
| | | | | © COPYRIGHT 19 | | BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT | |
| | | | | RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING | | | |
| | | | | TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO | | DIAM. ISOLANTE
(INS. DIA. RANGE) | |
| | | | | (TOLERANCES, UNLESS
OTHERWISE SPECIFIED) | | RANGO FILO
(WIRE RANGE) | |
| | | | | ± 0.3 | | SCALA
(SCALE) | |
| | | | | ANGOLI
(ANGLES) | | 2:1 | |
| | | | | $\pm 2^\circ$ | | Tyco Electronics | |
| | | | | DIS.
(DR.) | | Tyco Electronics AMP Italia S.r.l. | |
| | | | | CONT.
(CHK) | | Corso F.lli Corvi 15, Collegno (TO) | |
| | | | | DESCRIZIONE
(DESCRIPTION) | | 070 Sr. MULTILOCK* Conn. | |
| | | | | VEDERE FOGLIO 1 DI 4 | | CAP HOUSING ASS'Y 12 POSITION | |
| | | | | REV. | | VERTICAL TYPE | |
| | | | | REVISIONI
(REVISION RECORD) | | LOC. SIZE | |
| | | | | DIS. DATA
(DR) (DATE) | | NUMERO
(DWG NO) | |
| | | | | APP. —
(APP.) | | REV. | |
| | | | | | | FOGLIO
(SHEET) | |
| | | | | | | C1 | |
| | | | | | | 2 DI
(OF) | |
| | | | | | | C-282525 | |
| | | | | | | I A3 | |


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SEZIONE A-A
(SECTION A-A)

SCHEMA FORATURA CIRCUITO, SPESSORE 1.6 ± 0.2
(PCB HOLE PATTERN THICKNESS 1.6 ± 0.2)



DATARIO
(DATA CODE)

NUM. DI CAVITA'
(CIRCUIT IDENTIF. NO.)

1) BLOCCHETTO ADATTO PER CONTROPARTE P/N 282367-3 (12 VIE)
(HOUSING SUITABLE FOR PLUG 12 POSITION P/N 282367-3)

2) QUOTE MISURATE TRA I PIANI -X- E -Y-.
(DIMENSIONS MUST BE KEPT BETWEEN -X- AND -Y-).

3) TAB IN OTTONE STAGNATO.
(TAB: BRASS TIN PLATED).

4) FORO PER VITE AUTOFILETTANTE M3, DA APPLICARE PRIMA DELLA
STAGNATURA AD ONDA.
(HOLE FOR TAPPING SCREW M3, BEFORE SOLDER OPERATION)

BLU (BLUE)	PBT CARIC. VETRO (PBT G.F. FILLED)	282525-7
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)
± 0.3		2:1
ANGOLI (ANGLES)	Tyco Electronics Tyco Electronics AMP Italia S.r.l. Corso F.lli Cervi 15, Collegno (TO)	
DIS. (DR.)	DESCRIZIONE (DESCRIPTION) 070 Sr. MULTILOCK* Conn. CAP HOUSING ASS'Y 12 POSITION VERTICAL TYPE	
CONT. (CHK)	LOC. SIZE NUMERO (DWG NO)	REV. FOGLIO (SHEET)
VEDERE FOGLIO 1 DI 4	I A3 C-282525	C1 3 DI 4
REV. (REV.)	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)

