

**EH2525ETTS-1.843M TR**
[Click part number to visit Part Number Details page](#)
**REGULATORY COMPLIANCE** (Data Sheet downloaded on Nov 27, 2016)
[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.

**ITEM DESCRIPTION**

Quartz Crystal Clock Oscillators XO (SPXO) HCMOS/TTL (CMOS) 5.0Vdc 4 Pad 5.0mm x 7.0mm Ceramic Surface Mount (SMD) 1.843MHz  $\pm 25$ ppm -40°C to +85°C

**ELECTRICAL SPECIFICATIONS**

|                                       |                                                                                                                                                                                                                                        |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                     | 1.843MHz                                                                                                                                                                                                                               |
| Frequency Tolerance/Stability         | $\pm 25$ ppm Maximum (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration) |
| Aging at 25°C                         | $\pm 5$ ppm/year Maximum                                                                                                                                                                                                               |
| Operating Temperature Range           | -40°C to +85°C                                                                                                                                                                                                                         |
| Supply Voltage                        | 5.0Vdc $\pm 10\%$                                                                                                                                                                                                                      |
| Input Current                         | 50mA Maximum (No Load)                                                                                                                                                                                                                 |
| Output Voltage Logic High (Voh)       | 2.4Vdc Minimum with TTL Load, Vdd-0.4Vdc Minimum with HCMOS Load (IOH= -16mA)                                                                                                                                                          |
| Output Voltage Logic Low (Vol)        | 0.4Vdc Maximum with TTL Load, 0.5Vdc Maximum with HCMOS Load (IOL= +16mA)                                                                                                                                                              |
| Rise/Fall Time                        | 6nSec Maximum (Measured at 0.8Vdc to 2.0Vdc with TTL Load; Measured at 20% to 80% of waveform with HCMOS Load)                                                                                                                         |
| Duty Cycle                            | 50 $\pm 10$ (%) (Measured at 1.4Vdc with TTL Load; Measured at 50% of waveform with HCMOS Load)                                                                                                                                        |
| Load Drive Capability                 | 10TTL Load or 50pF HCMOS Load Maximum                                                                                                                                                                                                  |
| Output Logic Type                     | CMOS                                                                                                                                                                                                                                   |
| Pin 1 Connection                      | Tri-State (High Impedance)                                                                                                                                                                                                             |
| Tri-State Input Voltage (Vih and Vil) | +2.2Vdc Minimum to enable output, +0.8Vdc Maximum to disable output (High Impedance), No Connect to enable output.                                                                                                                     |
| Absolute Clock Jitter                 | $\pm 250$ pSec Maximum, $\pm 100$ pSec Typical                                                                                                                                                                                         |
| One Sigma Clock Period Jitter         | $\pm 50$ pSec Maximum, $\pm 30$ pSec Typical                                                                                                                                                                                           |
| Start Up Time                         | 10mSec Maximum                                                                                                                                                                                                                         |
| Storage Temperature Range             | -55°C to +125°C                                                                                                                                                                                                                        |


**ENVIRONMENTAL & MECHANICAL SPECIFICATIONS**

|                              |                                               |
|------------------------------|-----------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 1, HBM: 1500V |
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A         |
| Flammability                 | UL94-V0                                       |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C         |
| Mechanical Shock             | MIL-STD-883, Method 2002, Condition B         |
| Moisture Resistance          | MIL-STD-883, Method 1004                      |
| Moisture Sensitivity         | J-STD-020, MSL 1                              |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K          |
| Resistance to Solvents       | MIL-STD-202, Method 215                       |
| Solderability                | MIL-STD-883, Method 2003                      |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B         |
| Vibration                    | MIL-STD-883, Method 2007, Condition A         |

EH2525ETTS-1.843M TR [Click part number to visit Part Number Details page](#)



MECHANICAL DIMENSIONS (all dimensions in millimeters)




| PIN | CONNECTION     |
|-----|----------------|
| 1   | Tri-State      |
| 2   | Ground         |
| 3   | Output         |
| 4   | Supply Voltage |

| LINE | MARKING                                               |
|------|-------------------------------------------------------|
| 1    | ECLIPTEK                                              |
| 2    | 1.8430M                                               |
| 3    | XXXXXX<br>XXXXXX=Ecliptek<br>Manufacturing Identifier |


Suggested Solder Pad Layout

All Dimensions in Millimeters



All Tolerances are ±0.1

OUTPUT WAVEFORM & TIMING DIAGRAM




EH2525ETTS-1.843M TR

 Click part number to visit  
Part Number Details page


Test Circuit for TTL Output

| Output Load<br>Drive Capability | R <sub>L</sub> Value<br>(Ohms) | C <sub>L</sub> Value<br>(pF) |
|---------------------------------|--------------------------------|------------------------------|
| 10TTL                           | 390                            | 15                           |
| 5TTL                            | 780                            | 15                           |
| 2TTL                            | 1100                           | 6                            |
| 10LSTTL                         | 2000                           | 15                           |
| 1TTL                            | 2200                           | 3                            |

Table 1: R<sub>L</sub> Resistance Value and C<sub>L</sub> Capacitance Value Vs. Output Load Drive Capability



- Note 1: An external 0.1µF low frequency tantalum bypass capacitor in parallel with a 0.01µF high frequency ceramic bypass capacitor close to the package ground and V<sub>DD</sub> pin is required.
- Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.
- Note 3: Capacitance value C<sub>L</sub> includes sum of all probe and fixture capacitance.
- Note 4: Resistance value R<sub>L</sub> is shown in Table 1. See applicable specification sheet for 'Load Drive Capability'.
- Note 5: All diodes are MMBD7000, MMBD914, or equivalent.

**EH2525ETTS-1.843M TR**
[Click part number to visit Part Number Details page](#)
**Test Circuit for CMOS Output**

Note 1: An external  $0.1\mu\text{F}$  low frequency tantalum bypass capacitor in parallel with a  $0.01\mu\text{F}$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance ( $<12\text{pF}$ ), 10X attenuation factor, high impedance ( $>10\text{Mohms}$ ), and high bandwidth ( $>300\text{MHz}$ ) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.



# EH2525ETTS-1.843M TR

## Tape & Reel Dimensions

Quantity Per Reel: 1,000 units

All Dimensions in Millimeters

Compliant to EIA-481



EH2525ETTS-1.843M TR [Click part number to visit Part Number Details page](#)




Recommended Solder Reflow Methods



High Temperature Infrared/Convection

|                                            |  |                                                   |
|--------------------------------------------|--|---------------------------------------------------|
| <b>Ts MAX to TL (Ramp-up Rate)</b>         |  | 3°C/Second Maximum                                |
| <b>Preheat</b>                             |  |                                                   |
| - Temperature Minimum (Ts MIN)             |  | 150°C                                             |
| - Temperature Typical (Ts TYP)             |  | 175°C                                             |
| - Temperature Maximum (Ts MAX)             |  | 200°C                                             |
| - Time (ts MIN)                            |  | 60 - 180 Seconds                                  |
| <b>Ramp-up Rate (TL to TP)</b>             |  | 3°C/Second Maximum                                |
| <b>Time Maintained Above:</b>              |  |                                                   |
| - Temperature (TL)                         |  | 217°C                                             |
| - Time (tL)                                |  | 60 - 150 Seconds                                  |
| <b>Peak Temperature (TP)</b>               |  | 260°C Maximum for 10 Seconds Maximum              |
| <b>Target Peak Temperature (TP Target)</b> |  | 250°C +0/-5°C                                     |
| <b>Time within 5°C of actual peak (tP)</b> |  | 20 - 40 Seconds                                   |
| <b>Ramp-down Rate</b>                      |  | 6°C/Second Maximum                                |
| <b>Time 25°C to Peak Temperature (t)</b>   |  | 8 Minutes Maximum                                 |
| <b>Moisture Sensitivity Level</b>          |  | Level 1                                           |
| <b>Additional Notes</b>                    |  | Temperatures shown are applied to body of device. |

**EH2525ETTS-1.843M TR**
[Click part number to visit Part Number Details page](#)
**Recommended Solder Reflow Methods****Low Temperature Infrared/Convection 240°C**

|                                            |                                                        |
|--------------------------------------------|--------------------------------------------------------|
| <b>TS MAX to TL (Ramp-up Rate)</b>         | 5°C/Second Maximum                                     |
| <b>Preheat</b>                             |                                                        |
| - Temperature Minimum (TS MIN)             | N/A                                                    |
| - Temperature Typical (TS TYP)             | 150°C                                                  |
| - Temperature Maximum (TS MAX)             | N/A                                                    |
| - Time (ts MIN)                            | 60 - 120 Seconds                                       |
| <b>Ramp-up Rate (TL to TP)</b>             | 5°C/Second Maximum                                     |
| <b>Time Maintained Above:</b>              |                                                        |
| - Temperature (TL)                         | 150°C                                                  |
| - Time (tL)                                | 200 Seconds Maximum                                    |
| <b>Peak Temperature (TP)</b>               | 240°C Maximum                                          |
| <b>Target Peak Temperature (TP Target)</b> | 240°C Maximum 2 Times / 230°C Maximum 1 Time           |
| <b>Time within 5°C of actual peak (tP)</b> | 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time |
| <b>Ramp-down Rate</b>                      | 5°C/Second Maximum                                     |
| <b>Time 25°C to Peak Temperature (t)</b>   | N/A                                                    |
| <b>Moisture Sensitivity Level</b>          | Level 1                                                |
| <b>Additional Notes</b>                    | Temperatures shown are applied to body of device.      |

**Low Temperature Manual Soldering**

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

**High Temperature Manual Soldering**

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)