

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

|     |
|-----|
| LOC |
|-----|

|  |      |
|--|------|
|  | DIST |
|--|------|

## REVISIONS

AF

50

|  |   |
|--|---|
|  | F |
|--|---|

|     |
|-----|
| LTR |
|-----|

DESCRIPTION

DATE \_\_\_\_\_

|  |     |
|--|-----|
|  | DWN |
|--|-----|

|  |      |
|--|------|
|  | APVD |
|--|------|

14

REVISÉD PER ECR-12-013445



18OCT12

KH

|  |    |
|--|----|
|  | PD |
|--|----|




1 DIM'S IN BRACKETS ARE IN INCHES.

## 2 CONTINUOUS STRIP ON REELS.



```
- FITS .250 SERIES
FASTON TAB
```

VIEW A—A


$$\frac{3.94}{3.30} \left[ \frac{.155}{.130} \right]$$

$$\begin{array}{r} 5.37 \\ 5.33 \end{array} \quad \begin{array}{r} .255 \\ .210 \end{array}$$
$$\frac{5.59}{4.95} \left[ \frac{.220}{.195} \right]$$
$$\frac{5.59}{4.95} \quad \frac{.220}{.195}$$

SECT C-C

SECT B-B

|                              |                                       |                                      |         |
|------------------------------|---------------------------------------|--------------------------------------|---------|
| 3.05-4.32<br>[.120-.170] DIA | 0.8-2.0mm <sup>2</sup><br>[18-14] AWG | 0.81 <sup>+0.025</sup> [.032] [.001] | 41202   |
| INSUL RANGE                  | WIRE SIZE                             | MATING TAB THK                       | PART NO |

|                       |                |                                     |      |                         |                            |                                                                                                                                        |                                                                                       |                                                                                       |                       |                  |                                                                                                       |  |  |              |                 |
|-----------------------|----------------|-------------------------------------|------|-------------------------|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------------|------------------|-------------------------------------------------------------------------------------------------------|--|--|--------------|-----------------|
| 0                     | 4.57<br>[.180] | 6.4<br>[.252]                       | F    | 3.05<br>[.120]          | 1.90 [075]                 | 2.0mm <sup>2</sup> [14]                                                                                                                | THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                                                                       | DWN<br>JR RUTH        | 2/7/86           |  TE Connectivity |  |  |              |                 |
|                       |                | 1.68 [065]                          |      | 1.3mm <sup>2</sup> [16] | DIMENSIONS:<br>mm [INCHES] | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± 0.25 [.010]<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |                                                                                       | CHK<br>G YETTER                                                                       | 2/7/86                |                  |                                                                                                       |  |  |              |                 |
|                       |                | 1.55 [061]                          |      | 0.8mm <sup>2</sup> [18] |                            |                                                                                                                                        |                                                                                       |  | APVD<br>C MEYERS      | 2/7/86           | NAME<br><br>RECEPTACLE, FASTON,<br>6.35 [.250] SERIES                                                 |  |  |              |                 |
| TYPE                  | WIDTH          | STRIP<br>LENGTH<br>±0.38<br>[±.015] | TYPE | WIDTH                   | ±.051 [±.002]<br>HEIGHT    | WIRE                                                                                                                                   |  | PRODUCT SPEC<br>—                                                                     | APPLICATION SPEC<br>— | WEIGHT<br>—      |                                                                                                       |  |  |              | SIZE            |
| INSUL BARREL<br>CRIMP |                |                                     | WIRE | BARREL CRIMP            |                            |                                                                                                                                        |                                                                                       | MATERIAL<br><br>BRASS                                                                 | FINISH<br><br>—       | CUSTOMER DRAWING |                                                                                                       |  |  | SCALE<br>NTS | SHEET<br>1 OF 1 |