

Technical Data Sheet

Aquaseal® Fire-Alarm Cables



WEST PENN WIRE

2833 West Chestnut Street
Washington, PA 15301
Toll Free: (800) 245-4964
Fax: (724) 222-6420
www.westpenn-wpw.com



PART NUMBER:	AQ225
DESCRIPTION:	16/2 Stranded bare copper conductors, overall unshielded with Aquaseal tape and overall jacket.
NEC RATING:	FPL – PLTC, CL3 NEC Article 760 And 725
APPROVALS:	(UL) Listed - Direct Burial
APPLICATION:	Materials suitable for outdoor use, and indoor trays, allows a variety of uses for (Low voltage industrial process control circuits, Power-Limited circuits, Power-Limited fire alarm circuits, Power-Limited tray cable PLTC)

Construction Parameters:

Conductor	16 AWG Bare Copper
Stranding	7x24
Insulation Material	PVC with Nylon
Insulation Thickness	PVC 0.015" Nom. Nylon .005" Nom.
Number of Conductors	2 (1 Pair)
Shield	None
Drain	None
Water-Blocking Tape	2 Ply water swellable tape
Jacket Material	Sunlight/ Moisture Resistant PVC
Jacket Thickness	0.040" Nom.
Overall Cable Diameter	0.295" Nom.
Approximate Cable Weight	48 Lbs/1M' Nom.
Flame Rating	UL 1685 Vertical Tray

Electrical & Environmental Properties:

Temperature Rating	-20deg C to 90deg C
Operating Voltage	300 V RMS
Max.Capacitance Between Conductors @ 1 KHz	28 pf/ft Nom.
DC Resistance per Conductor @ 20deg C	4.2 Ohms/1M' Nom.
Insulation Colors	Black, Red
Jacket Color	Black
RoHS Compliant	--
TIA455-82B Water Infiltration Test Compliant	Yes
UL 444 & 13 Compliant	Yes

Mechanical Properties:

Max. Recommended Pull Tension	54 lbs.
Min. Bend Radius (Install)	2.9"

Specification Issue Date: 7/06

This document is the property of West Penn Wire.
The information contained herein is considered
Proprietary and not to be reproduced by any means
Without written consent of West Penn Wire

Standard Lengths are 1000ft.
The Jacket is sequentially footmarked.
The information presented here is, to the best of our
knowledge, is true and accurate. However, since
conditions of use are beyond our control, all
recommendations or suggestions are presented
without guarantee or responsibility on our part. We
disclaim all liability in connection with the use of
information contained herein or otherwise.