

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19085-0003](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: Open Barrel Ring , Brass, for 14-18 AWG Wire, Stud Size 10 (M5)

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-006 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19085](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Solderless Terminals](#)
Product Name N/A
Type Ring
UPC 800755080278

Physical

Barrel Type Open
Insulation None
Material - Plating Mating Tin
Net Weight 0.818/g
Packaging Type Reel
Stud Size 10 (M5)
Temperature Range - Operating 149°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter N/A
Wire Size AWG 14, 16, 18
Wire Size mm² 0.80 - 2.00

Electrical

Voltage - Maximum 2000V

Material Info

Old Part Number RZ-0129-10

Reference - Drawing Numbers

Product Specification PS-19902-006, PS-19902-011
Sales Drawing SD-19085-002




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19085Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
ASP Perishable Tool Kit used in ASP presses that process metal strip product	0190290053
Mini-Mac™ Applicator	0638815600

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19085-0003](#)