


## Trench™ Power MOSFETs

## IXTH110N25T IXTV110N25TS

$$\begin{aligned} V_{DSS} &= 250V \\ I_{D25} &= 110A \\ R_{DS(on)} &\leq 24m\Omega \end{aligned}$$


N-Channel Enhancement Mode  
Avalanche Rated  
Fast Intrinsic Rectifier




| Symbol       | Test Conditions                                                          | Maximum Ratings  |                  |
|--------------|--------------------------------------------------------------------------|------------------|------------------|
| $V_{DSS}$    | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                          | 250              | V                |
| $V_{DGR}$    | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ , $R_{GS} = 1M\Omega$    | 250              | V                |
| $V_{GSS}$    | Continuous                                                               | $\pm 20$         | V                |
| $V_{GSM}$    | Transient                                                                | $\pm 30$         | V                |
| $I_{D25}$    | $T_C = 25^\circ\text{C}$                                                 | 110              | A                |
| $I_{L(RMS)}$ | External Lead Current Limit                                              | 75               | A                |
| $I_{DM}$     | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$               | 300              | A                |
| $I_A$        | $T_C = 25^\circ\text{C}$                                                 | 25               | A                |
| $E_{AS}$     | $T_C = 25^\circ\text{C}$                                                 | 1                | J                |
| $P_D$        | $T_C = 25^\circ\text{C}$                                                 | 694              | W                |
| $dv/dt$      | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$ | 10               | V/ns             |
| $T_J$        |                                                                          | -55 to +150      | $^\circ\text{C}$ |
| $T_{JM}$     |                                                                          | +150             | $^\circ\text{C}$ |
| $T_{stg}$    |                                                                          | -55 to +150      | $^\circ\text{C}$ |
| $T_L$        | 1.6mm (0.063in) from Case for 10s                                        | 300              | $^\circ\text{C}$ |
| $T_{SOLD}$   | Plastic Body for 10s                                                     | 260              | $^\circ\text{C}$ |
| $M_d$        | Mounting Torque (to-247)                                                 | 1.13/10          | Nm/lb.in.        |
| $F_c$        | Mounting force (PLUS220SMD)                                              | 11..65/2.5..14.6 | N/lb.            |
| Weight       | TO-247                                                                   | 6                | g                |
|              | PLUS220SMD                                                               | 4                | g                |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |      |               |
|--------------|-----------------------------------------------------------------------------|-----------------------|------|---------------|
|              |                                                                             | Min.                  | Typ. | Max.          |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu A$                                            | 250                   |      | V             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 1mA$                                             | 3.0                   |      | 5.0 V         |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                          |                       |      | $\pm 200$ nA  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$                                          |                       |      | 5 $\mu A$     |
|              | $T_J = 125^\circ\text{C}$                                                   |                       |      | 250 $\mu A$   |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Notes 1, 2                     |                       |      | 24 m $\Omega$ |

TO-247 (IXTH)



PLUS220SMD(IXTV\_S)



G = Gate      D = Drain  
S = Source    Tab = Drain

### Features

- International Standard Packages
- Avalanche Rated
- High Current Handling Capability
- Fast Intrinsic Rectifier
- Low  $R_{DS(on)}$

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC Motor Drives
- Uninterruptible Power Supplies

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                                                                        | Characteristic Values |      |                        |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|------------------------|
|              |                                                                                                                                                    | Min.                  | Typ. | Max.                   |
| $g_{fs}$     | $V_{DS} = 10\text{V}$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                                                                                         | 65                    | 110  | S                      |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                                   |                       | 9400 | pF                     |
| $C_{oss}$    |                                                                                                                                                    |                       | 850  | pF                     |
| $C_{rss}$    |                                                                                                                                                    |                       | 55   | pF                     |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 15\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$<br>$R_G = 2\Omega$ (External) |                       | 19   | ns                     |
| $t_r$        |                                                                                                                                                    |                       | 27   | ns                     |
| $t_{d(off)}$ |                                                                                                                                                    |                       | 60   | ns                     |
| $t_f$        |                                                                                                                                                    |                       | 27   | ns                     |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 25\text{A}$                                                                          |                       | 157  | nC                     |
| $Q_{gs}$     |                                                                                                                                                    |                       | 40   | nC                     |
| $Q_{gd}$     |                                                                                                                                                    |                       | 50   | nC                     |
| $R_{thJC}$   |                                                                                                                                                    | 0.25                  |      | $0.18^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                    |                       |      | $^\circ\text{C/W}$     |


### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                             | Characteristic Values |      |               |
|----------|---------------------------------------------------------------------------------------------------------|-----------------------|------|---------------|
|          |                                                                                                         | Min.                  | Typ. | Max.          |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                    |                       |      | 110 A         |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                             |                       |      | 350 A         |
| $V_{SD}$ | $I_F = 55\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1                                                      |                       |      | 1.2 V         |
| $t_{rr}$ | $I_F = 55\text{A}$ , $-di/dt = 250\text{A}/\mu\text{s}$ ,<br>$V_R = 100\text{V}$ , $V_{GS} = 0\text{V}$ |                       | 170  | ns            |
| $I_{RM}$ |                                                                                                         |                       | 27   | A             |
| $Q_{RM}$ |                                                                                                         |                       | 2.3  | $\mu\text{C}$ |

### Notes:

- Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .
- On through-hole package,  $R_{DS(ON)}$  kelvin test contact location must be 5mm or less from the package body.


### TO-247 Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source

| Dim.           | Millimeter<br>Min. Max. | Inches<br>Min. Max. |
|----------------|-------------------------|---------------------|
| A              | 4.7 5.3                 | .185 .209           |
| A <sub>1</sub> | 2.2 2.54                | .087 .102           |
| A <sub>2</sub> | 2.2 2.6                 | .059 .098           |
| b              | 1.0 1.4                 | .040 .055           |
| b <sub>1</sub> | 1.65 2.13               | .065 .084           |
| b <sub>2</sub> | 2.87 3.12               | .113 .123           |
| C              | .4 .8                   | .016 .031           |
| D              | 20.80 21.46             | .819 .845           |
| E              | 15.75 16.26             | .610 .640           |
| e              | 5.20 5.72               | 0.205 0.225         |
| L              | 19.81 20.32             | .780 .800           |
| L1             | 4.50                    | .177                |
| ØP             | 3.55 3.65               | .140 .144           |
| Q              | 5.89 6.40               | 0.232 0.252         |
| R              | 4.32 5.49               | .170 .216           |
| S              | 6.15 BSC                | .242 BSC            |

### PLUS220SMD Outline




Terminals: 1 - Gate 2,4 - Drain  
3 - Source

| SYM | INCHES  |      | MILLIMETER |       |
|-----|---------|------|------------|-------|
|     | MIN     | MAX  | MIN        | MAX   |
| A   | .169    | .185 | 4.30       | 4.70  |
| A1  | .028    | .035 | 0.70       | 0.90  |
| A2  | .098    | .118 | 2.50       | 3.00  |
| A3  | .000    | .010 | 0.00       | 0.25  |
| b   | .035    | .047 | 0.90       | 1.20  |
| b1  | .080    | .095 | 2.03       | 2.41  |
| b2  | .054    | .064 | 1.37       | 1.63  |
| c   | .028    | .035 | 0.70       | 0.90  |
| D   | .551    | .591 | 14.00      | 15.00 |
| D1  | .512    | .539 | 13.00      | 13.70 |
| E   | .394    | .433 | 10.00      | 11.00 |
| E1  | .331    | .346 | 8.40       | 8.80  |
| e   | .200BSC |      | 5.08 BSC   |       |
| L   | .209    | .228 | 5.30       | 5.80  |
| L1  | .118    | .138 | 3.00       | 3.50  |
| L2  | .035    | .051 | 0.90       | 1.30  |
| L3  | .047    | .059 | 1.20       | 1.50  |
| L4  | .039    | .059 | 1.00       | 1.50  |


IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$**



**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 55\text{A}$  Value vs. Junction Temperature**



**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 55\text{A}$  Value vs. Drain Current**



**Fig. 6. Maximum Drain Current vs. Case Temperature**




Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance







Fig. 12. Maximum Transient Thermal Impedance




**Fig. 13. Resistive Turn-on**  
**Rise Time vs. Junction Temperature**




**Fig. 14. Resistive Turn-on**  
**Rise Time vs. Drain Current**




**Fig. 15. Resistive Turn-on**  
**Switching Times vs. Gate Resistance**



**Fig. 16. Resistive Turn-off**  
**Switching Times vs. Junction Temperature**



**Fig. 17. Resistive Turn-off**  
**Switching Times vs. Drain Current**



**Fig. 18. Resistive Turn-off**  
**Switching Times vs. Gate Resistance**

