

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [46557-3347](#)  
**Status:** **Active**  
**Overview:** [SEARAY\\*](#)  
**Description:** 1.27mm by 1.27mm Pitch SEARAY\* Slim Receptacle, 120 Circuits, 6.50mm Unmated Height, 4 Rows, with Pegs, Solder Charge™ Tin-Lead

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-45970-001 \(PDF\)](#)  
[Application Specification AS-45970-001 \(PDF\)](#)  
[Application Specification AS-45970-002 \(PDF\)](#)  
[Application Specification AS-45970-990 \(PDF\)](#)  
[Test Summary TS-45970-001 \(PDF\)](#)  
[Test Summary TS-45970-002 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                         |
|----------------|-------------------------|
| Product Family | PCB Receptacles         |
| Series         | <a href="#">46557</a>   |
| Application    | Board-to-Board, Signal  |
| Overview       | <a href="#">SEARAY*</a> |
| Product Name   | SEARAY*                 |
| UPC            | 883906530501            |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Circuits (Loaded)              | 120                            |
| Circuits (maximum)             | 120                            |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 100                            |
| Flammability                   | 94V-0                          |
| Glow-Wire Compliant            | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | No                             |
| Material - Metal               | Copper Alloy                   |
| Material - Plating Mating      | Gold, Nickel                   |
| Material - Plating Termination | Tin-Lead                       |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.673/g                        |
| Number of Rows                 | 4                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 1.60mm                         |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 2.18mm                         |
| Packaging Type                 | Embossed Tape on Reel          |
| Pitch - Mating Interface       | 1.27mm                         |
| Pitch - Termination Interface  | 1.27mm                         |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 2.540µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Robotic Placement              | Pick and Place Cap             |
| Stackable                      | No                             |
| Surface Mount Compatible (SMC) | No                             |



**EU RoHS**  
**Not RoHS Compliant**  
**REACH SVHC**  
Not Reviewed  
**Low-Halogen Status**  
**Low-Halogen**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[46557Series](#)

**Mates With**  
[46556](#) Searay\* Slim Plug Connector

|                               |                 |
|-------------------------------|-----------------|
| Temperature Range - Operating | -55°C to +125°C |
| Termination Interface: Style  | Through Hole    |
| Unmated Height                | 6.50mm          |

**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 2.7A    |
| Grounding to PCB              | No      |
| Voltage - Maximum             | 240V AC |

**Solder Process Data**

|                                                |                           |
|------------------------------------------------|---------------------------|
| Duration at Max. Process Temperature (seconds) | 60                        |
| Lead-free Process Capability                   | Reflow Capable (SMT only) |
| Max. Cycles at Max. Process Temperature        | 1                         |
| Process Temperature max. C                     | 230                       |
| Replacement RoHS Compliant Part Number         | 0465573345                |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                          |
|---------------------------|------------------------------------------|
| Application Specification | AS-45970-001, AS-45970-002, AS-45970-990 |
| Electrical Model Document | EE-45970-010                             |
| Product Specification     | PS-45970-001                             |
| S-Parameter Model         | SP-45970-010_REVA                        |
| Sales Drawing             | SD-46557-001                             |
| Test Summary              | TS-45970-001, TS-45970-002               |

\*SEARAY is a trademark of Samtec, Inc.